

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1619505       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB31          |
| Product key                          | ABRAEB        |
| GTIN                                 | 4046356823500 |
| Weight per piece (including packing) | 92.4 g        |
| Weight per piece (excluding packing) | 85.495 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

## Technical data

### Notes

|                    |                                            |
|--------------------|--------------------------------------------|
| Order information: | Order crimp contacts 6 x Ø 2 mm separately |
|--------------------|--------------------------------------------|

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|                                                        |                                                               |
|--------------------------------------------------------|---------------------------------------------------------------|
| Note                                                   | Order information: Order crimp contacts 6 x Ø 2 mm separately |
| Coding                                                 | N                                                             |
| Material (Insulating body)                             | PA 6.6                                                        |
| Connection method                                      | Crimp connection                                              |
| Contact switching type                                 | Pin                                                           |
| Application                                            | Signal                                                        |
| Number of positions                                    | 6                                                             |
| Direction of rotation                                  | Standard                                                      |
| Connection profile                                     | 6                                                             |
| Number Contact (Signal contacts)                       | 6                                                             |
| Diameter Contact (Signal contacts)                     | 2 mm                                                          |
| Litz wire cross-section min. Contact (Signal contacts) | 1 mm <sup>2</sup>                                             |
| Litz wire cross-section max. Contact (Signal contacts) | 2.5 mm <sup>2</sup>                                           |
| Rated current Contact (Signal contacts)                | 20 A (for max. connection cross section)                      |
| Rated voltage Contact (Signal contacts)                | 48 V AC                                                       |
|                                                        | 74 V DC                                                       |
| Rated surge voltage                                    | 1.5 kV                                                        |
| Overvoltage category                                   | III                                                           |
| Degree of pollution                                    | 3                                                             |

#### Housing

|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Cable connector housing |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | SPEEDCON                |
| Pg screw connection               | none                    |
| Housing material                  | CuZn, GD-Zn             |
| Degree of protection (plugged in) | IP67                    |

#### Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material           | NBR               |

### Environmental and real-life conditions

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

## Ambient conditions

|                                          |                   |
|------------------------------------------|-------------------|
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |

# CA-06P1N8A8008S - Cable connector


1619505

<https://www.phoenixcontact.com/us/products/1619505>



## Drawings

Schematic diagram



Connector pin assignment


# CA-06P1N8A8008S - Cable connector

1619505

<https://www.phoenixcontact.com/us/products/1619505>



Schematic diagram



Connector pin assignment

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619505>

|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                                |                                |                   |                               |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                          | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                    |                                |                                |                   |                               |
|                                                                                                                                          | 48 V                           | 10 A                           | 14                | -                             |

|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                                |                                |                   |                               |
|-----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                         | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                   |                                |                                |                   |                               |
|                                                                                                                                         | 48 V                           | 17 A                           | 14                | -                             |

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-06P1N8A8008S - Cable connector



1619505

<https://www.phoenixcontact.com/us/products/1619505>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 9a9ff783-eba8-4b90-b51e-cf1fa954d6cc |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)