

# SACC-M 8MS-3CON-M-0,34-SH - Connector



1542884

<https://www.phoenixcontact.com/us/products/1542884>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 3-position, shielded, Plug straight M8, coding: A, Screw connection, knurl material: Brass, nickel-plated, external cable diameter 3.5 mm ... 5.5 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

## Commercial data

Item number	1542884
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF30
Product key	AF2BBA
GTIN	4046356097826
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85366990
Country of origin	DE

# SACC-M 8MS-3CON-M-0,34-SH - Connector



1542884

<https://www.phoenixcontact.com/us/products/1542884>

## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---

### Mounting

Assembly note	The wires can be connected both with ferrules (without insulation) and without ferrules.
---------------	--

### Product properties

Product type	Circular connector (cable-side)
Sensor type	Universal
Number of positions	3
No. of cable outlets	1
Shielded	yes
Coding	A
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Length	55 mm

### External dimensions

Outside diameter	3.5 mm ... 5.5 mm
------------------	-------------------

### Housing

Diameter housing	14 mm
------------------	-------

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	Brass, nickel-plated
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

# SACC-M 8MS-3CON-M-0,34-SH - Connector



1542884

<https://www.phoenixcontact.com/us/products/1542884>

Material for screw connection

Brass, nickel-plated

## Connection data

### Conductor connection

Connection method	Screw connection
Connection cross section	0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (without ferrule) 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (with ferrule) 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (solid)
Connection cross section AWG	26 ... 20 (without ferrule)
Stripping length of the individual wire	4 mm
Tightening torque	0.2 Nm (M8 knurl) 0.3 Nm ... 0.4 Nm (Pressure screw for outer cable diameter 3 mm ... 4 mm) 0.8 Nm ... 1 Nm (Pressure screw for outer cable diameter 4 mm .. . 8 mm) 0.1 Nm (Screw terminal blocks)

## Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U <sub>N</sub>	48 V AC 60 V DC
Nominal current I <sub>N</sub>	4 A

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Plug
Head cable outlet	straight
Head thread type	M8
Coding	A

## Cable/line

Signal type/category	Universal
Stripping length of the individual wire	4 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
----------------------	------

# SACC-M 8MS-3CON-M-0,34-SH - Connector

1542884

<https://www.phoenixcontact.com/us/products/1542884>



Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)
---	----------------------------------

## Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

# SACC-M 8MS-3CON-M-0,34-SH - Connector


1542884

<https://www.phoenixcontact.com/us/products/1542884>




## Drawings

Dimensional drawing



Plug M8 x 1, straight, shielded

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

# SACC-M 8MS-3CON-M-0,34-SH - Connector

1542884

<https://www.phoenixcontact.com/us/products/1542884>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1542884>

UL Listed		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		60 V	4 A	-	-

cUL Listed		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		60 V	4 A	-	-

# SACC-M 8MS-3CON-M-0,34-SH - Connector

1542884

<https://www.phoenixcontact.com/us/products/1542884>



## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-M 8MS-3CON-M-0,34-SH - Connector

1542884

<https://www.phoenixcontact.com/us/products/1542884>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bf31e00d-b797-4f07-9cd3-cd40ca5e3f61

### EF3.0 Climate Change

CO2e kg	1.902 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)