

RC-19S1N12Z700 - Cable connector



1602943

<https://www.phoenixcontact.com/us/products/1602943>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, angled, shielded: no, Screw locking mechanism, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1602943
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	AB31
Product key	ABRAFC
GTIN	4046356242516
Weight per piece (including packing)	240.9 g
Weight per piece (excluding packing)	142.392 g
Customs tariff number	85366990
Country of origin	DE

RC-19S1N12Z700 - Cable connector



1602943

<https://www.phoenixcontact.com/us/products/1602943>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Number Contact (Contact group 1)	3
Diameter Contact (Contact group 1)	1.5 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	16
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Number Contact (Contact group 3)	1
Diameter Contact (Contact group 3)	1.5 mm
Rated current Contact (Contact group 3)	8 A

Housing

Order information:	Order contact inserts and cable clamping separately
--------------------	---

RC-19S1N12Z700 - Cable connector



1602943

<https://www.phoenixcontact.com/us/products/1602943>

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	Pg13,5
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-19S1N12Z700 - Cable connector


1602943

<https://www.phoenixcontact.com/us/products/1602943>



Drawings

Schematic diagram



Connector pin assignment


RC-19S1N12Z700 - Cable connector

1602943

<https://www.phoenixcontact.com/us/products/1602943>



Schematic diagram



Connector pin assignment


RC-19S1N12Z700 - Cable connector

1602943

<https://www.phoenixcontact.com/us/products/1602943>



Schematic diagram



Dimensional drawing

RC-19S1N12Z700 - Cable connector



1602943

<https://www.phoenixcontact.com/us/products/1602943>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-19S1N12Z700 - Cable connector



1602943

<https://www.phoenixcontact.com/us/products/1602943>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ef9b1bb3-6bf2-4ee1-9009-b729ed08a385

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com