

# VS-09-BU-DSUB-CD-G - D-SUB contact support



1688845

<https://www.phoenixcontact.com/us/products/1688845>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 1, for nine signal contacts, type of contact socket, for crimp contacts, straight, fixing with M thread, for panel mounting frame VS-09-...



## Commercial data

Item number	1688845
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918822972
Weight per piece (including packing)	11.4 g
Weight per piece (excluding packing)	11.4 g
Customs tariff number	85366990
Country of origin	DE

# VS-09-BU-DSUB-CD-G - D-SUB contact support

1688845

<https://www.phoenixcontact.com/us/products/1688845>



## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	9
Connection profile	D-SUB
Number of slots	1
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	17.9 mm
Height	12.93 mm
Length	31.19 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

### Environmental and real-life conditions

Ambient conditions	
--------------------	--

# VS-09-BU-DSUB-CD-G - D-SUB contact support

1688845

<https://www.phoenixcontact.com/us/products/1688845>



Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 130 °C

## Mounting

Mounting type	Screw mounting
---------------	----------------

# VS-09-BU-DSUB-CD-G - D-SUB contact support

1688845

<https://www.phoenixcontact.com/us/products/1688845>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688845>



**UL Recognized**  
Approval ID: E118976

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 9.0	EC001132
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-09-BU-DSUB-CD-G - D-SUB contact support

1688845

<https://www.phoenixcontact.com/us/products/1688845>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f4b36fc9-0270-4ca1-b728-6ba1d1aca751

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)