

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LED signal light, 3 colors, 24 V DC, point design



Product description

The signal light is intended for signaling functional states in machines and systems. The multi-colored LED signal light has a robust, UV-resistant housing with an M22 thread for mounting. The device is connected via a 5-pos. M12 connector and can be controlled with positive or negative switching. Numerous signaling functions and high color rendering index ensure smart and clear signaling. The signal light is equipped with active temperature management to extend the LED service life.

Your advantages

- Function-oriented signaling
- Large signaling range
- Clear identification of system states
- Quick and easy mounting and installation
- Electronically and mechanically robust design

Commercial data

Item number	1691142
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL112
GTIN	4067923252936
Weight per piece (including packing)	64.6 g
Weight per piece (excluding packing)	48 g
Customs tariff number	85318070
Country of origin	AT

PSD-SL GN/AM/RD-P - Optical signaling device

1691142

<https://www.phoenixcontact.com/us/products/1691142>



Technical data

Product properties

Product type	Signaling device
Product family	PSD-SL

Electrical properties

Switch-on time	< 10 ms
----------------	---------

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Max. current consumption	185 mA (Triple flash)

General

Maximum inrush current	0.5 A
Current consumption	60 mA
Signal element type	optical
Type of optical signal	Permanent light
	Blinking light
	Color change
	Triple flash

Output data

Leakage current	1 mA
-----------------	------

Connection data

Connection method	M12 connector, 5-pos.
-------------------	-----------------------

Signaling

Light properties

Source of light type	LED
Service life, lighting appliance	60000 h
Luminous intensity	21 Cd (Green)

Dimensions

Item dimensions

Height	65 mm
Diameter	50 mm

Calotte

Height	34 mm
--------	-------

Material specifications

PSD-SL GN/AM/RD-P - Optical signaling device

1691142

<https://www.phoenixcontact.com/us/products/1691142>



Material ()	Polycarbonate (UV stabilized)
-------------	-------------------------------

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 0.4 g ... 12 g, 10 Hz ... 55 Hz, amplitude 1.0 mm, sweep 5 min., dwell time 30 min.
Vibration resistance in accordance with MIL-STD-202F	: 10g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 30g, 11 ms period, half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection (IP)	IP66
	IP67
	IP69
	IP6K9K (In accordance with ISO 20653)
Degree of protection (IK)	IK08 (Impact resistance level)
Degree of protection (UL type)	UL Type 4
	UL Type 4X
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Single-hole mounting (M22 thread)
Mounting position	any

PSD-SL GN/AM/RD-P - Optical signaling device


1691142

<https://www.phoenixcontact.com/us/products/1691142>



Drawings

Dimensional drawing



Dimensions (in mm)

PSD-SL GN/AM/RD-P - Optical signaling device

1691142

<https://www.phoenixcontact.com/us/products/1691142>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1691142>



cULus Listed

Approval ID: E140324

PSD-SL GN/AM/RD-P - Optical signaling device

1691142

<https://www.phoenixcontact.com/us/products/1691142>



Classifications

ECLASS

ECLASS-13.0	27371220
ECLASS-15.0	27371220

ETIM

ETIM 9.0	EC000232
----------	----------

UNSPSC

UNSPSC 21.0	46171600
-------------	----------

PSD-SL GN/AM/RD-P - Optical signaling device

1691142

<https://www.phoenixcontact.com/us/products/1691142>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com