


# TC-06S1N8AT0EQ - Cable connector

1612166

<https://www.phoenixcontact.com/us/products/1612166>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, angled, Bayonet locking, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 10.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1612166
Packing unit	8 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRIDA
GTIN	4046356367097
Weight per piece (including packing)	146.15 g
Weight per piece (excluding packing)	140.508 g
Country of origin	DE

# TC-06S1N8AT0EQ - Cable connector

1612166

<https://www.phoenixcontact.com/us/products/1612166>



## Technical data

### Notes

Order information:	Order crimp contacts Ø 2 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Number Contact (Contact group 1)	6
Diameter Contact (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overshoot category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Bayonet locking
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	3 mm ... 10.5 mm
Seal material	NBR

### Environmental and real-life conditions

#### Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

# TC-06S1N8AT0EQ - Cable connector


1612166

<https://www.phoenixcontact.com/us/products/1612166>



## Drawings

Schematic diagram



Connector pin assignment


# TC-06S1N8AT0EQ - Cable connector

1612166

<https://www.phoenixcontact.com/us/products/1612166>



Schematic diagram



Connector pin assignment

# TC-06S1N8AT0EQ - Cable connector

1612166

<https://www.phoenixcontact.com/us/products/1612166>



## Classifications

### ECLASS

ECLASS-13.0	27440312
ECLASS-15.0	27440312

### ETIM

ETIM 9.0	EC002641
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# TC-06S1N8AT0EQ - Cable connector

1612166

<https://www.phoenixcontact.com/us/products/1612166>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	316f9e18-0f61-4940-b535-667648e095af

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)