


Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through header, nominal cross section: 16 mm<sup>2</sup>, color: green, nominal current: 76 A, rated voltage (III/2): 1000 V, contact surface: Ag, contact connection type: Socket, number of potentials: 8, number of rows: 1, number of positions: 8, number of connections: 8, product range: DFK-IPC 16/..-GF-SH, pitch: 10.16 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 4.1 mm, number of solder pins per potential: 3, plug-in system: COMBICON PC 16, Electrical properties: shielded, Pin connector pattern alignment: Standard, locking: Screw locking mechanism, mounting method: Threaded flange, type of packaging: packed in cardboard

Your advantages

- Well-known mounting principle allows worldwide use
- Flange system enables secure fixing to the housing panel by means of tool-free snap-in locking or screws
- Inverted header with socket contacts for touch-proof device outputs or PCB/PCB connections
- Shroud for professional EMC shield feed-through on the inside of the device
- Screwable flange for superior mechanical stability
- Integrated double steel spring provides additional safety in the event of temperature and power fluctuations

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1703030                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA05                           |
| Product key                          | AAEWAC                         |
| GTIN                                 | 4046356031622                  |
| Weight per piece (including packing) | 35.6 g                         |
| Weight per piece (excluding packing) | 31.516 g                       |
| Customs tariff number                | 85366990                       |
| Country of origin                    | PL                             |

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030

<https://www.phoenixcontact.com/us/products/1703030>

## Technical data

### Product properties

|                           |                        |
|---------------------------|------------------------|
| Product type              | Feed-through header    |
| Product family            | DFK-IPC 16/..-GF-SH    |
| Product line              | COMBICON Connectors XL |
| Type                      | Feed-through header    |
| Number of positions       | 8                      |
| Pitch                     | 10.16 mm               |
| Number of connections     | 8                      |
| Number of rows            | 1                      |
| Number of potentials      | 8                      |
| Mounting type             | Threaded flange        |
| Pin layout                | Linear pinning         |
| Solder pins per potential | 3                      |
| Electrical characteristic | shielded               |

### Electrical properties

#### Properties

|                             |          |
|-----------------------------|----------|
| Nominal current $I_N$       | 76 A     |
| Nominal voltage $U_N$       | 1000 V   |
| Contact resistance          | 0.3 mΩ   |
| Rated voltage (III/3)       | 630 V    |
| Rated surge voltage (III/3) | 6 kV     |
| Rated voltage (III/2)       | 1000 V   |
| Rated surge voltage (III/2) | 8 kV     |
| Rated voltage (II/2)        | 1000 V   |
| Rated surge voltage (II/2)  | 6 kV     |
| Electrical characteristic   | shielded |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Wave soldering |
| Pin layout    | Linear pinning |

### Material specifications

#### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | completely silver-plated                                                         |
| Metal surface contact area (top layer)   | Silver (4 - 8 μm Ag)                                                             |
| Metal surface soldering area (top layer) | Silver (4 - 8 μm Ag)                                                             |

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030

<https://www.phoenixcontact.com/us/products/1703030>


## Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | green (6021) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 10.16 mm                                                                             |
| Width [w]             | 122.36 mm                                                                            |
| Height [h]            | 22 mm                                                                                |
| Length [l]            | 34.55 mm                                                                             |
| Installed height      | 19.9 mm                                                                              |
| Solder pin length [P] | 4.1 mm                                                                               |
| Pin dimensions        | 0.8 x 1.2 mm                                                                         |

## PCB design

|               |          |
|---------------|----------|
| Pin spacing   | 10.16 mm |
| Hole diameter | 1.7 mm   |

## Mechanical tests

### Visual inspection

|               |                     |
|---------------|---------------------|
| Specification | IEC 60512-1:2001-01 |
| Result        | Test passed         |

### Dimension check

|               |                     |
|---------------|---------------------|
| Specification | IEC 60512-1:2001-01 |
| Result        | Test passed         |

### Resistance of inscriptions

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030

<https://www.phoenixcontact.com/us/products/1703030>

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

## Polarization and coding

|               |                                    |
|---------------|------------------------------------|
| Specification | IEC 60512-7:1993-08 (Polarization) |
| Result        | Test passed                        |

## Contact holder in insert

|                                                |                     |
|------------------------------------------------|---------------------|
| Specification                                  | IEC 60512-8:1993-01 |
| Contact holder in insert<br>Requirements >20 N | Test passed         |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 50          |
| Insertion strength per pos. approx. | 10 N        |
| Withdraw strength per pos. approx.  | 9 N         |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 9                     |

### Insulation resistance

|                                              |                     |
|----------------------------------------------|---------------------|
| Specification                                | IEC 60512-2:1985-00 |
| Insulation resistance, neighboring positions | 10 <sup>12</sup> Ω  |

### Air clearances and creepage distances | 1. Insulation coordination

|                                                        |                   |
|--------------------------------------------------------|-------------------|
| Specification                                          | IEC 61984:2008-10 |
| Insulating material group                              | I                 |
| Comparative tracking index (IEC 60112)                 | CTI 600           |
| Rated insulation voltage (III/3)                       | 630 V             |
| Rated surge voltage (III/3)                            | 6 kV              |
| minimum clearance value - non-homogenous field (III/3) | 5.5 mm            |
| minimum creepage distance (III/3)                      | 8 mm              |
| Rated insulation voltage (III/2)                       | 1000 V            |
| Rated surge voltage (III/2)                            | 8 kV              |
| minimum clearance value - non-homogenous field (III/2) | 8 mm              |
| minimum creepage distance (III/2)                      | 8 mm              |
| Rated insulation voltage (II/2)                        | 1000 V            |
| Rated surge voltage (II/2)                             | 6 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 5.5 mm            |
| minimum creepage distance (II/2)                       | 5.5 mm            |

### Air clearances and creepage distances | 2. Insulation coordination

|                           |                     |
|---------------------------|---------------------|
| Specification             | IEC 60664-1:2020-05 |
| Insulating material group | I                   |

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030

<https://www.phoenixcontact.com/us/products/1703030>

|                                                        |           |
|--------------------------------------------------------|-----------|
| Comparative tracking index (IEC 60112)                 | CTI 600   |
| Rated insulation voltage (III/3)                       | 630 V     |
| Rated surge voltage (III/3)                            | 6 kV      |
| minimum clearance value - non-homogenous field (III/3) | 5.5 mm    |
| minimum creepage distance (III/3)                      | 8 mm      |
| Rated insulation voltage (III/2)                       | 1250 V DC |
| Rated surge voltage (III/2)                            | 8 kV      |
| minimum clearance value - non-homogenous field (III/2) | 8 mm      |
| minimum creepage distance (III/2)                      | 8 mm      |
| Rated insulation voltage (II/2)                        | 1500 V DC |
| Rated surge voltage (II/2)                             | 8 kV      |
| minimum clearance value - non-homogenous field (II/2)  | 8 mm      |
| minimum creepage distance (II/2)                       | 8 mm      |

## Environmental and real-life conditions

### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:1995-03       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

### Durability test

|                                        |                     |
|----------------------------------------|---------------------|
| Specification                          | IEC 60512-5:1992-08 |
| Impulse withstand voltage at sea level | 9.8 kV              |
| Contact resistance R <sub>1</sub>      | 0.3 mΩ              |
| Contact resistance R <sub>2</sub>      | 0.4 mΩ              |
| Insertion/withdrawal cycles            | 50                  |

### Climatic test

|                                   |                   |
|-----------------------------------|-------------------|
| Specification                     | ISO 6988:1985-02  |
| Corrosive stress                  | KFW 0.2 S/1 cycle |
| Thermal stress                    | 100 °C/168 h      |
| Power-frequency withstand voltage | 4.26 kV           |

### Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030


<https://www.phoenixcontact.com/us/products/1703030>

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|


## Drawings

Dimensional drawing




Sheet metal cutout for snap-on.

Dimensional drawing




Sheet metal cutout for screw connection.

Dimensional drawing



Diagram



Type: IPC 16/...-STF-10,16 with DFK-IPC 16/...-GF-SH-10,16



# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030

<https://www.phoenixcontact.com/us/products/1703030>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1703030>

|  <b>cULus Recognized</b><br>Approval ID: E60425-20040202 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                         | 300 V                 | 55 A                  | -                 | -                           |
| C                                                                                                                                         | 300 V                 | 55 A                  | -                 | -                           |
| D                                                                                                                                         | 600 V                 | 5 A                   | -                 | -                           |

|  <b>VDE approval of drawings</b><br>Approval ID: 40055586 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                      | 1000 V                | 76 A                  | -                 | -                           |

# DFK-IPC 16/ 8-GF-SH-10,16 - Feed-through header



1703030  
<https://www.phoenixcontact.com/us/products/1703030>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|