

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

Item number	1620158
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEG
GTIN	4046356818872
Weight per piece (including packing)	94.3 g
Weight per piece (excluding packing)	88.761 g
Customs tariff number	85366990
Country of origin	DE

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



## Technical data

### Notes

Order information:	Order 12 x 1 mm crimp contacts separately
Order information:	When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786601)

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

Connection 1	
--------------	--

Head design	Socket
-------------	--------

Insulating body	
-----------------	--

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Signal contacts)	12
Diameter Contact (Signal contacts)	1 mm
Litz wire cross-section min. Contact (Signal contacts)	0.08 mm <sup>2</sup>
Litz wire cross-section max. Contact (Signal contacts)	1 mm <sup>2</sup>
Rated current Contact (Signal contacts)	8 A (for max. connection cross section)
Rated voltage Contact (Signal contacts)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing	
---------	--

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



Degree of protection (plugged in)	IP67
Seal	
External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C
Permissible humidity (storage/transport)	50 % ... 65 %

# CA-12S1N8A90DN - Coupler connector


1620158

<https://www.phoenixcontact.com/us/products/1620158>



## Drawings

Schematic diagram



Connector pin assignment


# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



Schematic diagram



Connector pin assignment

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620158>

<b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	48 V	4 A	20	-

<b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	48 V	6 A	20	-

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-12S1N8A90DN - Coupler connector

1620158

<https://www.phoenixcontact.com/us/products/1620158>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4c907238-964d-4ac7-a6cf-3a3cdcafa328

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)