

K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector in molded plastic on both sides, series: KSH, M23-Socket, angled rotatable, -120° left/120° right, number of positions: 4+4+4+PE, type of locking: SPEEDCON, on M23-Pin, angled rotatable, -120° left/120° right, number of positions: 4+4+4+PE, type of locking: SPEEDCON, cable length: 15 m, shielded: yes, color of outer sheath: orange RAL 2003

Your advantages

- Transmission of signals, data, and power in just a single connector
- CAT5 data interface for up to 100 Mbps
- Customer-specific assemblies and cable lengths can be supplied
- Simple and safe: 100% electrically tested and assembled ready for use
- Designs with preassembled cables on one or both sides
- Easy connection: angled design with configurable cable outlet direction
- Customer-specific assemblies and cable lengths can be supplied

Commercial data

Item number	1627579
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ABRDGG
GTIN	4055626326900
Weight per piece (including packing)	297.29 g
Weight per piece (excluding packing)	297.29 g
Country of origin	DE

K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Technical data

Product properties

Product type	Signal and power cable
--------------	------------------------

Connector

Connector specifications

Type	angled rotatable, -120° left/120° right
Housing material	PUR
Thread type	M23
Type of locking	SPEEDCON
Degree of protection	IP67, when in locked state IP68, when in locked state
No. of pos.	4+4+4+PE
Direction of rotation	Standard
Contact switching type	Socket
Insertion/withdrawal cycles	100
Voltage	630 V AC
Overshoot category	III
Degree of pollution	3
Rated surge voltage	6 kV

Cable specifications

Cable type	HDSL11Y-J
Transmission speed	CAT5
Transmission speed	100 Mbps (Data interface)
Shielded	yes
Cable structure	(5x 2.5 + 2x (2x 0.5) + (4x 0.34)C) C
External cable diameter	15.50 mm ±0.5 mm
Outer sheath, material	PUR
Material wire insulation	TPE
External sheath, color	orange RAL 2003
Single wire, color	black 1, black 2, black 3, black 4, green/yellow Power wires + PE brown, violet, black 5, green Signal wires blue, yellow, white, orange Data wires
Nominal voltage, cable	1000 V (300 V signal)
Test voltage	4 kV (1.5 kV signal)
Rated current	26 A (Power, in accordance with DIN VDE 0298-4 Tab. 11/5, at 15°C) 8 A (Signal, according to DIN VDE 0298-4 tab. 11/5) 3.6 A (Data, according to DIN VDE 0298-4 tab. 11/5)
Smallest bending radius, fixed installation	73 mm

K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Smallest bending radius, movable installation	148 mm
Max. bending cycles	1000000
Traversing path	6 m
Acceleration	30 m/s ²
Ambient temperature (operation) for fixed installation	-40 °C ... 80 °C (fixed installation)
Ambient temperature (operation) for flexible installation	-20 °C ... 80 °C (flexible installation)
UL AWM style	20234 / 10492 (80°C/1000 V)
Special properties	Flexible cable conduit capable
Flame resistance	IEC 60332-1-2
Halogen-free	in accordance with EN 50267-2-1
Resistance to oil	EN 60811-2-1

Connector specifications (second page)

Type	angled rotatable, -120° left/120° right
Housing material	PUR
Thread type	M23
Type of locking	SPEEDCON
Degree of protection	IP67, when in locked state
	IP68, when in locked state
No. of pos.	4+4+4+PE
Direction of rotation	Standard
Contact switching type	Pin
Insertion/withdrawal cycles	100
Voltage	630 V AC
Overshoot category	III
Degree of pollution	3
Rated surge voltage	6 kV

Electrical properties

Max. current	26 A
--------------	------

Cable/line

Cable length	15 m
--------------	------

K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides




1627579

<https://www.phoenixcontact.com/us/products/1627579>

Drawings

Dimensional drawing



Socket side, dimension A = 0 mm


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Dimensional drawing



Pin side; dimension A = ~ 0.3 mm


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Schematic diagram



Socket pin assignment


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in
molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Schematic diagram



Pin assignment of pin


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Schematic diagram



Cable outlet direction


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Schematic diagram



Cable outlet direction


K-8E-M23MK/15,0-H00/M23FK-C5-S - Connector in molded plastic on both sides



1627579

<https://www.phoenixcontact.com/us/products/1627579>

Circuit diagram



Contact assignment of M23 plugs/sockets

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com