

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, nominal current: 20 A, nominal cross section: 2.5 mm<sup>2</sup>, number of potentials: 1, number of rows: 1, number of positions per row: 1, product range: GKDS-EX, pitch: 7.5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: black, Pin layout: Linear pinning, Solder pin [P]: 5 mm, number of solder pins per potential: 2, type of packaging: packed in cardboard. The article can be aligned to create different nos. of positions! Every group of terminal blocks is to be provided with a GRZ 2,5V-EX (1706112) flange plate on both sides. If there are more than 10 terminal blocks, at least one additional flange plate must be mounted for each further group of ten. When the pitch spacer GRZ 2,5-EX (1724628) is used, the max. working voltage is increased to 420 V.

## Your advantages

- Well-known connection principle allows worldwide use
- Low temperature rise, thanks to maximum contact force
- Satisfies the more stringent safety requirements of "Ex e" protection according to IEC 60079-7 for potentially explosive areas
- Quick and convenient testing using integrated test option
- Two solder pins reduce the mechanical strain on the soldering spots
- The latching on the side enables various numbers of positions to be combined

## Commercial data

Item number	1709203
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AA13
Product key	AAMFGA
GTIN	4017918023638
Weight per piece (including packing)	4.317 g
Weight per piece (excluding packing)	3.991 g
Customs tariff number	85369010
Country of origin	DE

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



## Technical data

### Product properties

Product type	Printed circuit board terminal
Product family	GKDS-EX
Product line	COMBICON Terminals M
Type	PC terminal block can be aligned
Number of positions	1
Pitch	7.5 mm
Number of connections	1
Number of rows	1
Number of potentials	1
Pin layout	Linear pinning
Solder pins per potential	2

### Electrical properties

#### Properties

Nominal current $I_N$	20 A
Nominal voltage $U_N$	275 V
Rated current / conductor cross-section	20 A/2.5 mm <sup>2</sup>

### Connection data

#### Connection technology

Type	PC terminal block can be aligned
Nominal cross section	2.5 mm <sup>2</sup>

#### Conductor connection

Connection method	Screw connection with tension sleeve
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
2 conductors with same cross section, solid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
2 conductors with same cross section, flexible	0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Stripping length	9 mm
Drive form screw head	Slotted (L)
Tightening torque	0.5 Nm ... 0.6 Nm

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



## Mounting

Mounting type	Wave soldering
Pin layout	Linear pinning


## Material specifications

Material data - contact	
Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Tin-plated
Metal surface terminal point (top layer)	Tin (5 - 7 µm Sn)
Metal surface terminal point (middle layer)	Nickel (2 - 3 µm Ni)
Metal surface soldering area (top layer)	Tin (5 - 7 µm Sn)
Metal surface soldering area (middle layer)	Nickel (2 - 3 µm Ni)

## Material data - housing

Color (Housing)	black (9005)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

## Dimensions

Dimensional drawing	
Pitch	7.5 mm
Width [w]	7.5 mm
Height [h]	19.5 mm
Length [l]	19 mm
Installed height	20 mm
Solder pin length [P]	5 mm
Pin dimensions	1.1 x 0.8 mm

## PCB design

Hole diameter	1.4 mm
---------------	--------

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



## Electrical tests

Air clearances and creepage distances |

Insulating material group

I

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

## Packaging specifications

Type of packaging

packed in cardboard

# GKDS-EX - PCB terminal block


1709203

<https://www.phoenixcontact.com/us/products/1709203>




## Drawings

Dimensional drawing



Dimensional drawing



Installation instructions


# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



Schematic diagram



a = Flange plate, GRZ 2,5 V-EX

b = Terminal block GKDS-EX

c = Pitch spacer GRZ 2,5-EX


# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



Drilling plan/solder pad geometry



# GKDS-EX - PCB terminal block



1709203

<https://www.phoenixcontact.com/us/products/1709203>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1709203>

ATEX		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		275 V	20 A	-	0.2 - 2.5
Only rigid conductors		275 V	26 A	-	- 4
with pitch spacer		420 V	20 A	-	0.2 - 2.5

cUL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B		160 V	15 A	30 - 14	30 - 14
with pitch spacer		250 V	-	30 - 14	30 - 14
C		50 V	15 A	30 - 14	30 - 14
D		160 V	10 A	30 - 14	30 - 14
with pitch spacer		250 V	-	30 - 14	30 - 14

IECEx		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		275 V	20 A	-	0.2 - 2.5
Only rigid conductors		275 V	26 A	-	- 4
with pitch spacer		420 V	20 A	-	0.2 - 2.5

UL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B		160 V	15 A	30 - 14	-
with pitch spacer		250 V	-	30 - 14	-
C		50 V	15 A	30 - 14	-
D					

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



	160 V	10 A	30 - 14	-
with pitch spacer	250 V	-	30 - 14	-

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



## Classifications

### ECLASS

ECLASS-13.0	27460101
ECLASS-15.0	27460101

### ETIM

ETIM 9.0	EC002643
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# GKDS-EX - PCB terminal block

1709203

<https://www.phoenixcontact.com/us/products/1709203>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)