

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479

<https://www.phoenixcontact.com/us/products/1656479>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled FO cable, breakout cable, 980/1000 µm polymer fiber, SC-RJ/IP20 to SC-RJ/IP20, for installation inside control cabinets, the cable is suitable for UV-protected outdoor use, length: 5 m

Your advantages

- Reliable data transmission, thanks to high quality
- Fast data transmission for demanding applications
- Particularly suitable in EMC-sensitive applications
- Space savings in the control cabinet, thanks to SC-RJ connectors
- Preassembled patch cable for easy use

Commercial data

Item number	1656479
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIBA
GTIN	4046356029841
Weight per piece (including packing)	74.5 g
Weight per piece (excluding packing)	74.5 g
Customs tariff number	85447000
Country of origin	DE

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479

<https://www.phoenixcontact.com/us/products/1656479>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	2
Connection profile	SCRJ in accordance with DIN EN 50377-6-1
Number of slots	2

Electrical properties

Attenuation	< 2.5 dB (with 660 nm)
Transmission medium	FO

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 1000

Material specifications

Housing material	PBT
Contact material	Phosphor bronze
Outer sheath, material	PE

Connection data

Connection technology	
Connection method	POF SC-RJ

Conductor connection	
Connection method	POF SC-RJ

Connector

Connection 1	
Type	Plug straight SC-RJ
Handle color	black
Insertion/withdrawal cycles	≥ 1000
Degree of protection	IP20

Connection 2	
Type	Plug straight SC-RJ
Degree of protection	IP20

Cable/line

Cable length	5.00 m
Cable type	Polymer fiber (980 / 1000 µm)

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479

<https://www.phoenixcontact.com/us/products/1656479>

Cable type	Break-out cable
Outer sheath, material	PE
External sheath, color	black
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	30 mm
Ambient temperature (operation)	-20 °C ... 70 °C
	-20 °C ... 60 °C

FO cable

Number of fibers	2
Fiber	Polymer fiber, 980/1000 µm
Fiber type	POF fiber A4A
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation) (Cable, fixed installation)	-20 °C ... 70 °C
Ambient temperature (operation) (Cable, flexible installation)	-20 °C ... 60 °C
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable




1656479

<https://www.phoenixcontact.com/us/products/1656479>


Drawings

Dimensional drawing



SC-RJ connector, POD, IP20

Dimensional drawing



SC-RJ connector, POD, IP20


VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479


<https://www.phoenixcontact.com/us/products/1656479>

Schematic diagram



Pin assignment plug SCRJ

Schematic diagram



Pin assignment plug SCRJ

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479

<https://www.phoenixcontact.com/us/products/1656479>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 9.0	EC002607
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-PC-2XPOF-980-SCRJ/SCRJ-5 - FO connecting cable



1656479

<https://www.phoenixcontact.com/us/products/1656479>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2c35bba3-c935-4b37-9fdd-b1fbbf8e4435

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com