

# CK2,5-ED-1,50ST AU - Crimp contact



1674778

<https://www.phoenixcontact.com/us/products/1674778>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-06, Pin, turned, contact diameter: 2.5 mm, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16...16 , contact material: Cu alloy

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1674778       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BF65          |
| Product key                          | AF7AID        |
| GTIN                                 | 4017918135478 |
| Weight per piece (including packing) | 1.3 g         |
| Weight per piece (excluding packing) | 1.3 g         |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# CK2,5-ED-1,50ST AU - Crimp contact



1674778

<https://www.phoenixcontact.com/us/products/1674778>

## Technical data

### Notes

|               |                                                                                                                |
|---------------|----------------------------------------------------------------------------------------------------------------|
| General       | for HC-M-06..., HC-M-HV-, HC-M-08-, HC-M-20-, HC-A..., HC-B.., HC-BB..., HC-BBB..., and HC-HV contact carriers |
| Assembly note | The quality of a crimp connection is determined by DIN EN 60352-2.                                             |
| Assembly note | For voltages less than 5 V and currents less than 5 mA, gold-plated contacts are recommended.                  |

### Product properties

|                       |               |
|-----------------------|---------------|
| Product type          | Crimp contact |
| Series                | HC-M-06       |
|                       | HC-M-HV       |
|                       | HC-M-08       |
|                       | HC-A          |
|                       | HC-BB         |
|                       | HC-B          |
|                       | HC-HV         |
|                       | HC-M-20       |
|                       | HC-K          |
|                       | HC-BBB        |
|                       | HC-Q          |
|                       | HC-COM        |
|                       | HC-M-EMV      |
| Contact material type | turned        |

### Connection data

#### Connection technology

|                         |                  |
|-------------------------|------------------|
| Contact connection type | Pin              |
| Connection method       | Crimp connection |

#### Conductor connection

|                              |                                             |
|------------------------------|---------------------------------------------|
| Stripping length             | 7.5 mm (9.5 mm at HC-M-HV...)               |
| Connection cross section     | 1.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Connection cross section AWG | 16 ... 16                                   |

### Material specifications

|                          |          |
|--------------------------|----------|
| Material Contact         | Cu alloy |
| Material Contact surface | Au       |


### Dimensions

# CK2,5-ED-1,50ST AU - Crimp contact

1674778

<https://www.phoenixcontact.com/us/products/1674778>



|                             |                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Diameter (Contact diameter) | 2.5 mm                                                                             |

## Mechanical properties

|                             |       |
|-----------------------------|-------|
| Mechanical data             |       |
| Insertion/withdrawal cycles | ≥ 500 |

## Environmental and real-life conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient conditions              |                   |
| Ambient temperature (operation) | -40 °C ... 125 °C |

# CK2,5-ED-1,50ST AU - Crimp contact


1674778

<https://www.phoenixcontact.com/us/products/1674778>



## Drawings

Dimensional drawing



Dimensional drawing

# CK2,5-ED-1,50ST AU - Crimp contact

1674778

<https://www.phoenixcontact.com/us/products/1674778>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674778>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# CK2,5-ED-1,50ST AU - Crimp contact



1674778

<https://www.phoenixcontact.com/us/products/1674778>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440204 |
| ECLASS-15.0 | 27440204 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000796 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# CK2,5-ED-1,50ST AU - Crimp contact



1674778

<https://www.phoenixcontact.com/us/products/1674778>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)