

# VS-15-ST-DSUB-FK - D-SUB contact insert

1688890

<https://www.phoenixcontact.com/us/products/1688890>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact insert, shell size 2, with 15 signal contacts, type of contact pin, flat-ribbon cable connection, angled, fixing with a 3 mm hole, for panel mounting frame VS-15...



## Your advantages

- D-SUB 15 connection
- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

## Commercial data

Item number	1688890
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918823047
Weight per piece (including packing)	13.17 g
Weight per piece (excluding packing)	7.92 g
Customs tariff number	85366990
Country of origin	DE

# VS-15-ST-DSUB-FK - D-SUB contact insert

1688890

<https://www.phoenixcontact.com/us/products/1688890>



## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	1.5 A (at 20 °C)
Test voltage	1000 V
Transmission medium	Copper

### Connection data

Connection method	Flat-ribbon cable connection
-------------------	------------------------------

### Dimensions

Width	18.5 mm
Height	12.93 mm
Length	39.52 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel
Contact carrier material	Polyester GF

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 50

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-55 °C ... 125 °C

### Mounting

# VS-15-ST-DSUB-FK - D-SUB contact insert

1688890

<https://www.phoenixcontact.com/us/products/1688890>



Mounting type

Hole

# VS-15-ST-DSUB-FK - D-SUB contact insert

1688890

<https://www.phoenixcontact.com/us/products/1688890>



## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 9.0	EC001132
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-15-ST-DSUB-FK - D-SUB contact insert

1688890

<https://www.phoenixcontact.com/us/products/1688890>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)