

# VS-09-BU-DSUB/CAN - D-SUB contact insert

1689051

<https://www.phoenixcontact.com/us/products/1689051>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB CAN-BUS contact insert, type 09, version: Socket



## Commercial data

Item number	1689051
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AB12
Product key	ABNCAB
GTIN	4017918876814
Weight per piece (including packing)	11.92 g
Weight per piece (excluding packing)	10.678 g
Customs tariff number	85369010
Country of origin	DE

# VS-09-BU-DSUB/CAN - D-SUB contact insert

1689051

<https://www.phoenixcontact.com/us/products/1689051>



## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Connection profile	D-SUB
Number of slots	1
Shielded	yes

### Electrical properties

Transmission medium	Copper
Power transmission	Power

### Connection data

Connection method	Screw connection
-------------------	------------------

### Dimensions

Width	24 mm
Height	59.8 mm
Length	104.65 mm

### Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	tin-plated
Contact carrier material	PA

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20

### Mounting

Mounting type	Screw mounting
---------------	----------------

# VS-09-BU-DSUB/CAN - D-SUB contact insert

1689051

<https://www.phoenixcontact.com/us/products/1689051>



## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 9.0	EC001132
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-09-BU-DSUB/CAN - D-SUB contact insert

1689051

<https://www.phoenixcontact.com/us/products/1689051>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	45e6f9ad-136b-4f7e-b508-66f984537c0c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)