


1818766

<https://www.phoenixcontact.com/us/products/1818766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB headers, nominal cross section: 1.5 mm<sup>2</sup>, color: black, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Sn, contact connection type: Pin, number of potentials: 16, number of rows: 2, number of positions: 8, number of connections: 16, product range: DMCV 1,5/...G1F-THR, pitch: 3.5 mm, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 2 mm, number of solder pins per potential: 1, plug-in system: COMBICON DFMC 1,5, Pin connector pattern alignment: Standard, locking: Lock-and-release locking system, mounting method: Lock & Release, type of packaging: 56 mm wide tape

Your advantages

- Designed for integration into the SMT soldering process
- Vertical connection enables multi-row arrangement on the PCB
- Screwable flange for superior mechanical stability
- Automatic locking and intuitive release through Lock and Release operating lever in contrasting color
- Small component size for applications where space is at a premium

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1818766       |
| Packing unit                         | 220 pc        |
| Minimum order quantity               | 220 pc        |
| Product key                          | AABTJC        |
| GTIN                                 | 4046356757874 |
| Weight per piece (including packing) | 6.22 g        |
| Weight per piece (excluding packing) | 4.114 g       |
| Country of origin                    | DE            |

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766

<https://www.phoenixcontact.com/us/products/1818766>

## Technical data

### Product properties

|                           |                                |
|---------------------------|--------------------------------|
| Product type              | PCB headers                    |
| Product family            | DMCV 1,5/..-G1F-THR            |
| Product line              | COMBICON Connectors S          |
| Type                      | Headers                        |
| Number of positions       | 8                              |
| Pitch                     | 3.5 mm                         |
| Number of connections     | 16                             |
| Number of rows            | 2                              |
| Number of potentials      | 16                             |
| Mounting type             | Lock & release threaded flange |
| Pin layout                | Linear pinning                 |
| Solder pins per potential | 1                              |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 8 A    |
| Nominal voltage $U_N$       | 160 V  |
| Contact resistance          | 2.1 mΩ |
| Rated voltage (III/3)       | 160 V  |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 250 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | THR soldering  |
| Pin layout    | Linear pinning |

#### Flange

|                   |        |
|-------------------|--------|
| Tightening torque | 0.2 Nm |
|-------------------|--------|

#### Processing notes

|                                  |                       |
|----------------------------------|-----------------------|
| Process                          | Reflow/wave soldering |
| Moisture Sensitive Level         | MSL 1                 |
| Classification temperature $T_c$ | 260 °C                |
| Solder cycles in the reflow      | 3                     |

### Material specifications

#### Material data - contact

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766


<https://www.phoenixcontact.com/us/products/1818766>

|                                             |                                                                                  |
|---------------------------------------------|----------------------------------------------------------------------------------|
| Note                                        | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                            | Cu alloy                                                                         |
| Surface characteristics                     | Tin-plated                                                                       |
| Metal surface contact area (top layer)      | Tin (3 - 5 $\mu\text{m}$ Sn)                                                     |
| Metal surface contact area (middle layer)   | Nickel (1.3 - 3 $\mu\text{m}$ Ni)                                                |
| Metal surface soldering area (top layer)    | Tin (3 - 5 $\mu\text{m}$ Sn)                                                     |
| Metal surface soldering area (middle layer) | Nickel (1.3 - 3 $\mu\text{m}$ Ni)                                                |

## Material data - housing

|                                        |              |
|----------------------------------------|--------------|
| Color (Housing)                        | black (9005) |
| Insulating material                    | LCP          |
| Insulating material group              | IIIa         |
| CTI according to IEC 60112             | 175          |
| Flammability rating according to UL 94 | V0           |

## Dimensions

|                       |                                                                                      |
|-----------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 3.5 mm                                                                               |
| Width [w]             | 35 mm                                                                                |
| Height [h]            | 12 mm                                                                                |
| Length [l]            | 10.6 mm                                                                              |
| Installed height      | 10 mm                                                                                |
| Solder pin length [P] | 2 mm                                                                                 |
| Pin dimensions        | 0.8 x 0.8 mm                                                                         |

## PCB design

|               |         |
|---------------|---------|
| Pin spacing   | 5.50 mm |
| Hole diameter | 1.4 mm  |

## Mechanical tests

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
|---------------|------------------------|

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766

<https://www.phoenixcontact.com/us/products/1818766>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

## Contact holder in insert

|                                                |                        |
|------------------------------------------------|------------------------|
| Specification                                  | IEC 60512-15-1:2008-05 |
| Contact holder in insert<br>Requirements >20 N | Test passed            |

## Insertion and withdrawal forces

|                                     |             |
|-------------------------------------|-------------|
| Result                              | Test passed |
| No. of cycles                       | 25          |
| Insertion strength per pos. approx. | 3 N         |
| Withdraw strength per pos. approx.  | 2 N         |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 20                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | IIIa                |
| Comparative tracking index (IEC 60112)                 | CTI 175             |
| Rated insulation voltage (III/3)                       | 160 V               |
| Rated surge voltage (III/3)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm              |
| minimum creepage distance (III/3)                      | 2.5 mm              |
| Rated insulation voltage (III/2)                       | 160 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |
| minimum creepage distance (III/2)                      | 1.6 mm              |
| Rated insulation voltage (II/2)                        | 250 V               |
| Rated surge voltage (II/2)                             | 2.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 1.5 mm              |
| minimum creepage distance (II/2)                       | 2.5 mm              |

## Environmental and real-life conditions

### Vibration test

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60068-2-6:2007-12 |
|---------------|-----------------------|

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766

<https://www.phoenixcontact.com/us/products/1818766>

|                        |                             |
|------------------------|-----------------------------|
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

## Durability test

|                                        |                       |
|----------------------------------------|-----------------------|
| Specification                          | IEC 60512-9-1:2010-03 |
| Impulse withstand voltage at sea level | 2.95 kV               |
| Contact resistance $R_1$               | 2.1 m $\Omega$        |
| Contact resistance $R_2$               | 2.4 m $\Omega$        |
| Insertion/withdrawal cycles            | 25                    |


## Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 1.39 kV                                                                   |

## Ambient conditions


|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Packaging specifications


|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 56 mm wide tape                                                                      |
| [W] tape width              | 56 mm                                                                                |
| [W2] coil overall dimension | ≤ 62.4 mm                                                                            |
| [A] coil diameter           | ≤ 330 mm                                                                             |
| Outer packaging type        | Transparent-Bag                                                                      |

## Drawings

Dimensional drawing




Schematic diagram




Panel cutout

Schematic diagram




Use of the CP-DMC... coding profile

Diagram




Type: DFMC 1,5/...-STF-3,5 with DMCV 1,5/...-G1F-3,5-LR P...THR



Type: DFMC 1,5/...-ST-3,5-LR with DMCV 1,5/...-G1F-3,5-LR P20THR

Drilling plan/solder pad geometry





Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1818766>

|                                                                                                                                                       |                                |                                |                   |                               |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
| <div> <b>cULus Recognized</b><br/>Approval ID: E60425-20110128</div> |                                |                                |                   |                               |
|                                                                                                                                                       | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| B                                                                                                                                                     |                                |                                |                   |                               |
|                                                                                                                                                       | 300 V                          | 8 A                            | -                 | -                             |
| C                                                                                                                                                     |                                |                                |                   |                               |
|                                                                                                                                                       | 50 V                           | 8 A                            | -                 | -                             |
| D                                                                                                                                                     |                                |                                |                   |                               |
|                                                                                                                                                       | 300 V                          | 8 A                            | -                 | -                             |

|                                                                                                                                                                     |                                |                                |                   |                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
| <div> <b>VDE report with production monitoring</b><br/>Approval ID: 40038423</div> |                                |                                |                   |                               |
|                                                                                                                                                                     | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                                               |                                |                                |                   |                               |
|                                                                                                                                                                     | 160 V                          | 8 A                            | -                 | -                             |

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766

<https://www.phoenixcontact.com/us/products/1818766>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# DMCV 1,5/ 8-G1F-3,5-LRP20THRR56 - PCB header



1818766

<https://www.phoenixcontact.com/us/products/1818766>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)