

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Locking element for locking the top PCB onto UM-PRO housing close to the edge



Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2200168 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AC13 |
| Product key | ACHDAZ |
| GTIN | 4046356547611 |
| Weight per piece (including packing) | 0.315 g |
| Weight per piece (excluding packing) | 0.3 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|----------------|------------------------------|
| Product type | Mounting material |
| Housing type | Press-drawn section housings |
| Housing series | UM-PRO |
| Product family | UM-PRO |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |
| Surface characteristics | untreated |

Environmental and real-life conditions

| | |
|------------------|------------------------|
| Glow-wire test | |
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

| | |
|--------------------------------------|------------------------|
| Thermal stability / ball thrust test | |
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 125 °C |
| Test duration | 1 h |
| Force | 20 N |

| | |
|---------------------------------------|------------------------|
| Mechanical strength / tumbling barrel | |
| Specification | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm |
| Frequency | 50 |

| | |
|---|--|
| Ambient conditions | |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2200168>



UL Recognized

Approval ID: E240868

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-PRO PCB S-LOCK BK - Locking

2200168

<https://www.phoenixcontact.com/us/products/2200168>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com