

# FLKM 34/ZFKDS - Termination board

2302939

<https://www.phoenixcontact.com/us/products/2302939>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Standard 1:1 FLK module, with spring-cage connection and flat-ribbon cable connector, no. of positions 34



## Commercial data

Item number	2302939
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2181
GTIN	4017918941444
Weight per piece (including packing)	163 g
Weight per piece (excluding packing)	0.75 g
Customs tariff number	85369010
Country of origin	DE

# FLKM 34/ZFKDS - Termination board



2302939

<https://www.phoenixcontact.com/us/products/2302939>

## Technical data

### Product properties

Product type	Interface module
Number of positions	34

### Insulation characteristics

Insulation	Functional insulation
Ovvoltage category	II
Pollution degree	2

### Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

### Connection data

#### Field level

Connection method	Spring-cage connection
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	34
Pitch	2.54 mm

### Signaling

Status display present	no
------------------------	----

### Dimensions

#### Item dimensions

Width	90 mm
Height	77 mm
Depth	52.34 mm

### Material specifications

Color	green (RAL 6021)
-------	------------------

### Environmental and real-life conditions

# FLKM 34/ZFKDS - Termination board

2302939

<https://www.phoenixcontact.com/us/products/2302939>



## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM 34/ZFKDS - Termination board


2302939

<https://www.phoenixcontact.com/us/products/2302939>



## Drawings

Circuit diagram



# FLKM 34/ZFKDS - Termination board

2302939

<https://www.phoenixcontact.com/us/products/2302939>



## Classifications

### ETIM

ETIM 8.0

EC002780

### UNSPSC

UNSPSC 21.0

39121400

# FLKM 34/ZFKDS - Termination board

2302939

<https://www.phoenixcontact.com/us/products/2302939>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)