

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface module with 1:1 connection and separate equipotential terminals (suitable for analog output cards of the Delta V control system)

Your advantages

- These system-specific interface modules for DeltaV modules are used in combination with the relevant system cables
- 1:1 connection
- Separate potential terminal blocks per channel

Commercial data

Item number	2304429
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218K
GTIN	4017918981990
Weight per piece (including packing)	155.1 g
Weight per piece (excluding packing)	122.57 g
Customs tariff number	85369010
Country of origin	DE

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	16
No. of channels	8

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overshoot category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 1 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

Supported controller EMERSON DeltaV

Suitable I/O card	VE4003S2B4
-------------------	------------

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of positions	27
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² 0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve) 0.25 mm ² ... 2.5 mm ² (Ferrule with plastic sleeve)

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



Conductor cross-section flexible (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ² 0.2 mm ² ... 0.75 mm ² (Ferrule without plastic sleeve) 0.5 mm ² ... 0.5 mm ² (TWIN ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions	
Width	55.8 mm
Height	89.6 mm
Depth	79.3 mm

Material specifications

Color	gray (RAL 7042)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions	
Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA	
Certificate	UKCA-compliant

Standards and regulations

Air clearances and creepage distances	
Standards/regulations	EN IEC 60664-1

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning
--------------------	--

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



instructions of the respective third-party manufacturer must also be met.


FLKM 16/AI/DV - Termination board



2304429

<https://www.phoenixcontact.com/us/products/2304429>

Drawings



FLKM 16/AI/DV connection scheme

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM 16/AI/DV - Termination board

2304429

<https://www.phoenixcontact.com/us/products/2304429>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com