


MKDSB 3/ 3-B-5,08 GNYE - PCB terminal block



1907283

<https://www.phoenixcontact.com/us/products/1907283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, nominal cross section: 2.5 mm², number of potentials: 3, number of rows: 1, number of positions per row: 3, product range: MKDSB 3/..-B, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, mounting: Wave soldering, conductor/PCB connection direction: 0 °, color: green-yellow, Pin layout: Linear pinning, Solder pin [P]: 4 mm, number of solder pins per potential: 1, type of packaging: packed in cardboard

Your advantages

- Well-known connection principle allows worldwide use
- Low temperature rise, thanks to maximum contact force
- Allows connection of two conductors
- Internal bridging for easily looping through potentials
- The latching on the side enables various numbers of positions to be combined

Commercial data

Item number	1907283
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	AAMFIG
GTIN	4017918484576
Weight per piece (including packing)	6.39 g
Weight per piece (excluding packing)	6.026 g
Country of origin	PL

Technical data

Product properties

Product type	Printed circuit board terminal
Product family	MKDSB 3/..-B
Product line	COMBICON Terminals M
Number of positions	3
Pitch	5.08 mm
Number of connections	3
Number of rows	1
Number of potentials	3
Pin layout	Linear pinning
Solder pins per potential	1

Connection data

Conductor connection

Connection method	Screw connection with tension sleeve
Drive form screw head	Slotted (L)

Mounting

Mounting type	Wave soldering
Pin layout	Linear pinning

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Tin-plated
Metal surface terminal point (top layer)	Tin (5 - 7 µm Sn)
Metal surface terminal point (middle layer)	Nickel (2 - 3 µm Ni)
Metal surface soldering area (top layer)	Tin (5 - 7 µm Sn)
Metal surface soldering area (middle layer)	Nickel (2 - 3 µm Ni)

Material data - housing

Color (Housing)	green-yellow ()
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775

MKDSB 3/ 3-B-5,08 GNYE - PCB terminal block



1907283

<https://www.phoenixcontact.com/us/products/1907283>

Temperature for the ball pressure test according to EN 60695-10-2

125 °C


Notes

Note on application

For safe conductor connection, always adhere to a defined tightening torque. Particularly in the case of PCB terminal blocks with two or three positions, the individual solder pin for each contact point cannot compensate for this. That is why the terminal blocks must be supported during conductor connection (held with one hand, support on the housing).
--

Dimensions

Dimensional drawing



Pitch

5.08 mm

Width [w]

14.98 mm

Height [h]

23 mm

Length [l]

11.12 mm

Installed height

19 mm

Solder pin length [P]

4 mm

PCB design

Hole diameter

1.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-40 °C ... 100 °C (Depending on the current carrying capacity/derating curve)

Ambient temperature (storage/transport)

-40 °C ... 70 °C

Relative humidity (storage/transport)

30 % ... 70 %

Ambient temperature (assembly)

-5 °C ... 100 °C

Packaging specifications

Type of packaging

packed in cardboard

MKDSB 3/ 3-B-5,08 GNYE - PCB terminal block



1907283

<https://www.phoenixcontact.com/us/products/1907283>

Classifications

ECLASS

ECLASS-13.0	27460101
ECLASS-15.0	27460101

ETIM

ETIM 9.0	EC002643
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

MKDSB 3/ 3-B-5,08 GNYE - PCB terminal block



1907283

<https://www.phoenixcontact.com/us/products/1907283>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.06 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com