

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 22.9 cm / 9"-TFT display (analog resistive (polyester)), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Arm® Cortex®-A8, 800 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, Open platform, without bus system.

Commercial data

Item number	2400776
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABA
GTIN	4055626109992
Weight per piece (including packing)	1,300 g
Weight per piece (excluding packing)	1,300 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
Computer data	
Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
RAM	1 MB SRAM
	512 MB LPDDR RAM
Data storage system	NAND-Flash, 1 GB
Slots	1x SD

Display

Display type	22.9 cm / 9"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	640 cd/m ² typical (adjustable)
MTBF	70000 h
Color spectrum	16.7 million colors
Reading angle left	85.00 °
Reading angle right	85.00 °
Reading angle top	85.00 °
Reading angle bottom	85.00 °

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	Open platform

Electrical properties

Service life of battery	5 years (typical)

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.6 A

Real-time clock

Realtime clock	Yes

Mounting

Mounting type	Front mounting

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	260 mm / 172 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	252 mm / 164 mm / 54 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

Classifications

UNSPSC

UNSPSC 21.0

43211904

2400776

<https://www.phoenixcontact.com/us/products/2400776>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com