

IB ST ZF 24 TEMP 4 RTD - I/O module

2701959

<https://www.phoenixcontact.com/us/products/2701959>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS-ST analog input module, 4 inputs, RTD, 2-, 3-, and 4-conductor connection, IP20 degree of protection, consisting of: terminal part with spring-cage connection and module electronics

Product description

The module is designed for use within an ST station.
It is used to acquire signals from resistive temperature sensors.

Your advantages

- 4 analog input channels for connecting resistance temperature detectors (RTDs)
- Connection of sensors in 2-, 3-, and 4-conductor technology

Commercial data

Item number	2701959
Packing unit	1 pc
Sales key	DR03
Product key	DRI343
GTIN	4046356895880
Weight per piece (including packing)	562.8 g
Weight per piece (excluding packing)	562.8 g
Customs tariff number	85389091
Country of origin	DE

IB ST ZF 24 TEMP 4 RTD - I/O module



2701959

<https://www.phoenixcontact.com/us/products/2701959>

Technical data

Dimensions

Width	118 mm
Height	116 mm
Depth	117 mm

Interfaces

ST local bus

No. of channels	2
Connection method	ST local bus connector
Transmission speed	500 kbps
Transmission physics	Copper

Input data

Analog

Input name	Analog RTD inputs
Description of the input	Inputs for resistive temperature sensors
Number of inputs	4 (for resistance temperature detectors)
Connection technology	2-, 3-, 4-conductor (shielded)
A/D converter resolution	24 bit
Sensor types (RTD) that can be used	Pt 100, Pt 1000, Ni 100, Ni 1000
Measuring principle	Sigma/Delta process
Measured value representation	16 bit two's complement

Product properties

Product type	I/O component
Type	modular
	INTERBUS Smart Terminal
Operating mode	Process data mode with 4 words
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler
	F1 fuse failure I/O error message sent to the bus coupler
	I/O supply failure I/O error message sent to the bus coupler

Electrical properties

Maximum power dissipation for nominal condition	0.5 W
---	-------

Supply: Module electronics

Connection method	ST local bus connector
Designation	Communications power
Supply voltage	9 V DC (from the ST local bus)
Current consumption	typ. 54 mA

IB ST ZF 24 TEMP 4 RTD - I/O module



2701959

<https://www.phoenixcontact.com/us/products/2701959>

	max. 80 mA
Power consumption	typ. 0.5 W

Supply:

Designation	U _S
Supply voltage	24 V DC
Supply voltage range	19.5 V DC ... 30.2 V DC (including all tolerances, including ripple)
Current consumption	typ. 15 mA

Electrical isolation/isolation of the voltage ranges

Test voltage: Bus/Inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/inputs	500 V AC, 50 Hz, 1 min
Test voltage: Supply voltage/Ground conductor	500 V AC, 50 Hz, 1 min
Test voltage: I/O voltage/Ground conductor	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Terminal block
-----------------	----------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	8 mm

Terminal block

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

IB ST ZF 24 TEMP 4 RTD - I/O module



2701959

<https://www.phoenixcontact.com/us/products/2701959>

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB ST ZF 24 TEMP 4 RTD - I/O module



2701959

<https://www.phoenixcontact.com/us/products/2701959>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 8.0	EC001596
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB ST ZF 24 TEMP 4 RTD - I/O module



2701959

<https://www.phoenixcontact.com/us/products/2701959>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com