

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Digital output module, Functional safety, SafetyBridge technology, Digital outputs: 4 (for 2-channel assignment), 8 (for 1-channel assignment), 2 A, connection technology: 2-, 3-conductor, degree of protection: IP20

Product description

The safety module is an output module from the Axioline F product range for use in a SafetyBridge technology V3 system. The safety module can be used as part of an Axioline F station at any point within an EtherCAT®, EtherNet/IP™, Sercos, Modbus, PROFINET or PROFIBUS system. The module has four safe digital outputs for two-channel assignment or eight safe digital outputs for single-channel assignment. Depending on the installation and parameterization, in the SafetyBridge technology V3 system the safety module can achieve the following safety integrity:

- up to SIL 3 according to standard EN 61508
- up to SIL 3 according to standard EN IEC 62061
- up to Cat. 4/PL e according to standard EN ISO 13849-1

Your advantages

- Cost-effective system configuration, as no safety PLC or safe fieldbus system is required
- Flexible use, thanks to compatibility with all bus couplers from the Axioline F range
- Reduced installation time, thanks to fast wiring and easy handling
- Easy configuration using the free SAFECONF software
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508

Commercial data

Item number	2702264
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN03
Product key	DNA531
GTIN	4055626066806
Weight per piece (including packing)	350.9 g
Weight per piece (excluding packing)	222 g
Customs tariff number	85389091
Country of origin	DE

AXL F SSDO8/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Technical data

Dimensions

Dimensional drawing	
	53.6
	54
Width	53.6 mm
Height	126.1 mm
Depth	54 mm
Note on dimensions	Housing dimensions

Notes

Note on application

Note on application

Only for industrial use

Interfaces

Axioline F local bus

No. of channels	1
Connection method	Bus base module

System properties

Module

Input address area	8 Byte
Output address area	8 Byte
Required parameter data	1 Byte
Required configuration data	7 Byte

Output data

Digital:

Output name	Digital outputs
Connection method	Direct plug-in technology
Connection technology	2-, 3-conductor
Number of outputs	4 (for 2-channel assignment) 8 (for 1-channel assignment)
	8
Protective circuit	Overload protection, freewheeling circuit for inductive loads, Discharge circuit for accelerated discharge of capacitive loads

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Output voltage	24 V DC
Output current	max. 2 A (per channel) max. 1.5 A (per channel according to CUL _{US}) max. 4 A (per group) max. 3 A (per group according to CUL _{US}) max. 8 A (Total current of all outputs; Please observe the notes in the user manual.) max. 6 A (Total current of all outputs according to CUL _{US})
Maximum output current per channel	2 A
Maximum output current per module / terminal block	8 A
Behavior with overload	Affected output is disabled and a diagnostic message is generated.

Product properties

Product type	I/O component
Product family	Axioline F
Application	Functional safety SafetyBridge technology
Type	modular

Electrical properties

Transmission medium	Copper
Potentials	
Protective circuit	Protection against polarity reversal, EMC protective circuit, undervoltage detection

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
Current draw	max. 280 mA typ. 260 mA (all outputs set; supply by U _O of 19.2 V DC ... 30 V DC)

Potentials: Supply for digital output modules (U_O)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30.2 V DC (including all tolerances, including ripple)
Current draw	typ. 25 mA (all outputs set; supply from U _O with 30 V DC; without supply to the actuators)

Connection data

Connection technology	
Connection name	Axioline F connector
Conductor connection	
Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Axioline F connector

Connection method	Push-in connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-35 °C ... 60 °C (Mounting position: any)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 108 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 75 % (on average, 85% infrequently, non-condensing)
Permissible humidity (storage/transport)	10 % ... 75 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

AXL F SSD08/3 1F - Safety module




2702264


<https://www.phoenixcontact.com/us/products/2702264>

Drawings

Dimensional drawing



Connection diagram



Example connection of a contactor

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702264>



DNV GL

Approval ID: TAA00000DF

BSH

Approval ID: 840



cULus Listed

Approval ID: E238705



Functional Safety

Approval ID: 968/FSP 2449.00/22

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 9.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

AXL F SSD08/3 1F - Safety module

2702264

<https://www.phoenixcontact.com/us/products/2702264>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0b1318d0-75ef-4497-802e-c72b377a357b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com