

# PLD M 160 W-95/105 896 - LED machine light



2702478

<https://www.phoenixcontact.com/us/products/2702478>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED machine light, 24 V DC, emission angle (vertical/Horizontal): 95 °/105 °, length: 896 mm, degree of protection: IP67, can be swiveled, including mounting accessories

## Product description

This LED machine light is designed to provide illumination inside or on machinery. Due to the narrow design, it can be mounted even where space is at a premium. In the light holder supplied, the light can swivel and the lighting can therefore be optimally aligned. The satin-finished plastic cover prevents glare for the machine operator.

## Your advantages

- Narrow design enables mounting even in confined spaces
- Ready to connect by means of punched-on 3 m supply line
- Focused illumination, thanks to swivel action
- IP67 protection enables use even in wet environments
- ETL approval permits use on the North American market
- Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 50000 h

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2702478       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR08          |
| Product key                          | DRL221        |
| GTIN                                 | 4055626213842 |
| Weight per piece (including packing) | 1,200 g       |
| Weight per piece (excluding packing) | 800 g         |
| Customs tariff number                | 94054239      |
| Country of origin                    | DE            |

# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



## Technical data

### Notes

#### Note on application

Note on application

Only for industrial use

### Product properties

|                    |  |
|--------------------|--|
| Product type       | Machine light  |
| Application        | Machine  |
| Mounting position  | any  |
| Special properties | can be swiveled Swiveling range $\pm 35^\circ$<br>including mounting accessories |

### Electrical properties

#### Supply: Module electronics

|                      |   |
|----------------------|---|
| Connection method    | open cable end  |
| Cable length         | approx. 3 m   |
| Supply voltage       | 24 V DC   |
| Supply voltage range | 22 V DC ... 26 V DC   |
| Current consumption  | typ. 0.875 A (at 24 V DC)   |
| Power consumption    | approx. 21 W (at 24 V DC)   |
| Protective circuit   | Surge protection; Suppressor diode, 28 V DC<br>Reverse polarity protection; Polarity protection diode |

### Signaling

#### Light properties

|                         |  |
|-------------------------|--|
| Source of light type    | LED  |
| Number of LEDs          | 36   |
| Color temperature       | 6600 K $\pm 10\%$  |
| Color rendering index   | 75   |
| Luminous flux           | approx. 900 lm (Net luminous flux)   |
| Luminous efficacy       | approx. 43 lm/W  |
| Illumination            | max. 833 lx (50 cm distance)<br>min. 150 lx (Distance of 50 cm over 1 m <sup>2</sup> area) |
| Average illumination    | 449 lx (Distance of 50 cm over 1 m <sup>2</sup> area)                                      |
| Emission angle          | 95 ° (C0-C180)<br>105 ° (C90-C270)   |
| Ordinance               | Delegated Regulation (EU) 2019/2015  |
| Energy efficiency class | G (6 light sources)  |
| Note                    | This product contains energy efficiency class G light sources.                             |

### Dimensions


# PLD M 160 W-95/105 896 - LED machine light



2702478

<https://www.phoenixcontact.com/us/products/2702478>

## Dimensional drawing



Width

22.5 mm

Height

23 mm

Length

896 mm

## Material specifications

|             |  |
|-------------|--|
| Color       | aluminum color   |
| Material () | Anodized aluminum (Light housing)<br>Satinized acrylic (Light cover) |
|             |  |

## Environmental and real-life conditions

### Ambient conditions

|  |                       |
|--|-----------------------|
| Ambient temperature (operation)          | 0 °C ... 40 °C        |
| Degree of protection                     | IP67                  |
| Air pressure (operation)                 | 69 kPa ... 102 kPa    |
| Air pressure (storage/transport)         | 69 kPa ... 102 kPa    |
| Ambient temperature (storage/transport)  | -10 °C ... 50 °C      |
| Permissible humidity (operation)         | 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 95 % (non-condensing) |

### Energy labeling

|                         |   |
|-------------------------|---|
| Energy efficiency class | G |
|-------------------------|---|

## Standards and regulations

|                  |                                       |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

## Mounting

|                   |                  |
|-------------------|------------------|
| Mounting type     | Screw mounting   |
|                   | Snap-on assembly |
| Mounting position | any              |

# PLD M 160 W-95/105 896 - LED machine light


2702478

<https://www.phoenixcontact.com/us/products/2702478>



## Drawings

Dimensional drawing




# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



Diagram



Illuminance distribution  
(distance  $d = 0.5$  m)


# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



Diagram



Luminous intensity distribution (LID)  
(red line: C0 - C180, blue line: C90 - C270)

# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702478>



**ETLus**

Approval ID: LV-Lighting-Systems



**cETL**

Approval ID: Luminaires



**EAC**

Approval ID: TR\_TS\_D\_12879-22

# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27110345 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000348 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151500 |
|-------------|----------|

# PLD M 160 W-95/105 896 - LED machine light

2702478

<https://www.phoenixcontact.com/us/products/2702478>



## Environmental product compliance

### EU RoHS

|   |                      |
|---|----------------------|
| Fulfills EU RoHS substance requirements | Yes                  |
| Exemption                               | 6(a)-I, 7(a), 7(c)-I |

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |                      |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)