

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Industrial 3G router, European version, fallback to 2G GPRS/EDGE, 2 Ethernet interfaces, firewall, NAT, SMA-F antenna socket, SMS and e-mail transmission, 2 digital inputs, 1 digital output

Product description

The **TC ROUTER** for cellular communication implements high-performance data links of up to 150 Mbps via mobile 4G LTE networks. This enables you to establish a mobile broadband connection for highly flexible site networking even in places where a wired Internet connection is not available. These connections can be used to transmit sensitive data securely over mobile networks.

Your advantages

- Industrial 3G mobile router (UMTS/HSPA)
- Fallback to 2G (GPRS/EDGE)
- Networking of Ethernet end devices via the cellular network
- Ethernet SMS gateway for easy alerting
- Stateful inspection firewall for dynamic filtering
- NAT table and port forwarding for direct remote access to an end device
- Two switching inputs and one switching output
- Configuration via web-based management or microSD card
- Two local Ethernet connections
- Switchable energy-saving mode
- Integrated logbook
- Connection monitoring
- Extended temperature range of -40 °C ... +70 °C

Commercial data

Item number	2702531
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC422
GTIN	4055626212838
Weight per piece (including packing)	352.1 g
Weight per piece (excluding packing)	232.8 g
Country of origin	DE

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Technical data

Product properties

Product type	Cellular router
MTTF	383 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	184 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	78 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)

Security functions

Filtering	IP, port, protocol
Firewall rules	Stateful inspection firewall

Electrical properties

Electrical isolation	VCC // UMTS // Ethernet // PE
Mains type	Cellular communication

Supply

Supply voltage range	10 V DC ... 30 V DC (Via pluggable Push-in terminal block)
Typical current consumption	< 200 mA (24 V DC)
	65 mA (With activated energy-saving mode)

Max. current consumption

1.7 A

Function

Management	Web-based management, SNMP
------------	----------------------------

Input data

Digital

Description of the input	Digital input
Number of inputs	2
Voltage input signal	10 V DC ... 30 V DC
Switching level "1" signal	10 V DC ... 30 V DC

Output data

Signal

Output name	Digital output
Number of outputs	1
Voltage output signal	10 V DC ... 30 V DC (depending on the operating voltage)
Current output signal	≤ 50 mA (Not short-circuit proof)

Connection data

Supply

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Connection method	Push-in spring connection
Conductor cross-section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 0.75 mm ²
Single conductor/terminal point, rigid	0.14 mm ² ... 1.5 mm ²
Single-wire/terminal point, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	26 ... 16
Stripping length	9.00 mm

Interfaces

Signal	Ethernet
Web server	yes

Data: Ethernet interface, 10/100Base-T(X) in accordance with IEEE 802.3

Serial transmission speed	10/100 Mbps, auto negotiation
Connection method	RJ45 jack, shielded
No. of channels	2
Transmission length	100 m (shielded twisted pair)
Protocols supported	TCP/IP, UDP/IP, FTP, HTTP(S)
Auxiliary protocols	ARP, DHCP, PING (ICMP), SNMP V1/V2, SMTP(S), NTP, SSL/TLS, STARTTLS

Wireless

Interface description	GSM / GPRS / EDGE / UMTS / HSPA
Frequency range	900 MHz (UMTS/HSPA B8) 2100 MHz (UMTS/HSPA B1) 850 MHz (2 W (EGSM)) 900 MHz (2 W (EGSM)) 1800 MHz (1 W (EGSM)) 1900 MHz (1 W (EGSM))
Data rate	≤ 21.6 Mbps (HSPA (DL)) ≤ 5.76 Mbps (HSPA (UL))
Antenna	50 Ω impedance SMA antenna socket
Antenna connection method	SMA (female)
SIM Interface	1.8 volt, 3 volt
GPRS	Class 12, Class B CS1 ... CS4
EDGE	Multislot Class 10
UMTS	HSPA 3GPP R7

Dimensions


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Dimensional drawing



Width

45 mm

Height

130 mm

Depth

127 mm

Material specifications

Color (Upper housing part)	light gray (RAL 7035)
Material (Housing)	Plastic

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (Maximum transmission power 10 dBm)
	-40 °C ... 60 °C (Maximum transmission power 23 dBm)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Approvals

CE	
Certificate	CE-compliant

Corrosive gas test	
Identification	ISA-S71.04-1985 G3 Harsh Group A

EMC data

Electromagnetic compatibility	Conformance with RED Directive 2014/53/EU
Noise immunity	EN 61000-6-2

Electrostatic discharge	
Standards/regulations	EN 61000-4-2

Electrostatic discharge	
Contact discharge	± 6 kV (Test Level 3)

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Discharge in air	± 8 kV (Test Level 3)
Comments	Criterion B
Electromagnetic HF field	
Standards/regulations	EN 61000-4-3
Electromagnetic HF field	
Frequency range	80 MHz ... 3 GHz (Test Level 3)
Field intensity	10 V/m
Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Input	± 2 kV (Test Level 3)
Signal	± 2 kV (Ethernet)
Comments	Criterion B
Surge current load (surge)	
Standards/regulations	EN 61000-4-5
Surge current load (surge)	
Input	± 0.5 kV (symmetrical)
	± 1 kV (asymmetrical)
Signal	± 1 kV (Data line, asymmetrical)
Comments	Criterion B
Conducted interference	
Standards/regulations	EN 61000-4-6
Conducted interference	
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V
Emitted interference	
Radio interference voltage in acc. with EN 55011	Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	Class B, area of application: Industry and residential
Criteria	
Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.
Mounting	
Mounting type	DIN rail mounting

TC ROUTER 2002T-3G - Router


2702531

<https://www.phoenixcontact.com/us/products/2702531>



Drawings

Dimensional drawing




TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Connection diagram



Switching inputs


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Schematic diagram



Front view


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Schematic diagram



Connect the antenna


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Schematic diagram



Remove SIM card holder


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>

 **PHOENIX**
CONTACT

Schematic diagram



Insert the SIM card


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Schematic diagram



Device connections


TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Schematic diagram



Mounting

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Classifications

ECLASS

ECLASS-13.0	19170502
-------------	----------

ETIM

ETIM 9.0	EC001478
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

TC ROUTER 2002T-3G - Router

2702531

<https://www.phoenixcontact.com/us/products/2702531>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com