

# PSI-MOS-RS232/FO1300 E - FO converters



2708588

<https://www.phoenixcontact.com/us/products/2708588>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with integrated optical diagnostics, alarm contact, for RS-232 interfaces up to 115.2 kbps, termination device with one fiber optic interface (SC duplex), 1300 nm, for fiberglass cable

## Your advantages

- Connections can be plugged in via a COMBICON screw terminal block
- Supply voltage and data signals routed through the DIN rail connectors
- Redundant power supply possible by means of optional system power supply unit
- High-quality electrical isolation between all interfaces (RS-232 // fiber optic ports // power supply // DIN rail connector)
- Approved for use in zone 2
- Floating switch contact for advance warning of critical FO paths
- Integrated optical diagnostics for continuous monitoring of FO paths
- Automatic data rate detection for all data rates up to 115.2 kbps

## Commercial data

Item number	2708588
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC215
GTIN	4046356176286
Weight per piece (including packing)	245.8 g
Weight per piece (excluding packing)	183.78 g
Customs tariff number	85176200
Country of origin	DE

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
Utilization restriction	

#### CCCx note

Use in potentially explosive areas is not permitted in China.

## Product properties

Product type	Media converter
Product family	PSI-MOS
MTTF	942 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) 418 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%) 172 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
MTBF	549 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day)) 113 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

## Electrical properties

Electrical isolation	VCC // V.24 (RS-232)
Maximum power dissipation for nominal condition	2.5 W
Test voltage data interface/power supply	1.5 kV <sub>rms</sub> (50 Hz, 1 min.)

## Supply

Supply voltage range	18 V DC ... 32 V DC
Nominal supply voltage	24 V DC
Typical current consumption	100 mA (24 V DC)
Max. current consumption	≤ 2 A (For operation in a joining station, via the DIN rail connector)

## Output data

Switching	
Output name	Relay output
Output description	Alarm output
Number of outputs	1
Maximum switching voltage	60 V DC 42 V AC
Limiting continuous current	1 A

## Connection data

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



## Supply

Connection method	COMBICON plug-in screw terminal block
Single conductor/terminal point, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Single-wire/terminal point, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	24 ... 14
Stripping length	7.00 mm
Tightening torque	0.56 Nm ... 0.79 Nm

## Interfaces

Bit distortion, input	± 35 % (permitted)
Bit distortion, output	< 6.25 %
Signal	Modbus
Transmission channels	2 (1/1), RxD, TxD, full duplex

## Data: optical FO

No. of channels	1
Transmit capacity, minimum	-3.4 dBm (50/125 µm, multimode fiberglass)
	-4.7 dBm (62.5/125 µm, multimode fiberglass)
	-5.5 dBm (9/125 µm, singlemode fiberglass)
Transmission length incl. 3 dB system reserve	27 km (With F-G 50/125 0.7 dB/km at 1300 nm)
	22 km (with F-G 62.5/125 0.8 dB/km at 1300 nm)
	45 km (With F-E 9/125 0.4 dB/km at 1300 nm)
Transmission protocol	Transparent to protocol for RS-232 interface
Connection method	SC duplex
Wavelength	1300 nm
Minimum receiver sensitivity	-25.5 dBm (50/125 µm, multimode fiberglass)
	-25.5 dBm (62.5/125 µm, multimode fiberglass)
	-26.5 dBm (9/125 µm, singlemode fiberglass)
Maximum receiver sensitivity	0 dBm
Transmission medium	Multi-mode fiberglass
	Single-mode fiberglass

## Data: V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1

Serial transmission speed	9.6 Kbps ... 115.2 Kbps
Connection method	D-SUB 9 plug
Tightening torque	0.4 Nm
Transmission length	≤ 15 m
Transmission medium	Copper
File format/coding	UART (11 Bit, NRZ)
Data direction switching	Automatic control

## Dimensions


# PSI-MOS-RS232/FO1300 E - FO converters



2708588

<https://www.phoenixcontact.com/us/products/2708588>

## Dimensional drawing



Width

35 mm

Height

99 mm

Depth

105 mm

## Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA 6.6-FR

## Cable/line

### FO cable

Fiber types	50/125 µm
	9/125 µm
	Fiberglass

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g, 11 ms period, half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### ATEX

Identification	Ex II 3 G Ex ec nC IIC T4 Gc
Certificate	PxCIF07ATEX2708559X
Note	Please follow the special installation instructions in the documentation!

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



UL, USA/Canada

Identification	508 Listed 508 Recognized
----------------	------------------------------

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 55011
-----------------------	----------

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	± 6 kV
Discharge in air	± 8 kV
Comments	Criterion B

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Field intensity	10 V/m
Comments	Criterion A

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Input	± 2 kV
Signal	± 2 kV
Comments	Criterion B

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Input	± 0.5 kV
Signal	± 1 kV
Comments	Criterion B

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



Comments	Criterion A
Voltage	10 V

## Emitted interference

Standards/regulations	EN 55011
Comments	Class A, industrial applications

## Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

## Standards and regulations

Free from substances that could impair the application of coating	VDMA 24364:2018-05
---	--------------------

## Mounting

Mounting type	DIN rail mounting
Useable DIN rail type	DIN rail: 35 mm

# PSI-MOS-RS232/FO1300 E - FO converters




2708588

<https://www.phoenixcontact.com/us/products/2708588>

## Drawings

Dimensional drawing



Housing dimensions


# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



Application drawing



Point-to-point connection


# PSI-MOS-RS232/FO1300 E - FO converters



2708588

<https://www.phoenixcontact.com/us/products/2708588>

Application drawing



Star structure


# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



Schematic diagram



Connecting data cables


## PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>

**PHÖNIX CONTACT**

## Block diagram



## Basic circuit diagram

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2708588>



**cULus Listed**

Approval ID: E238705



**cULus Recognized**

Approval ID: E238705



**ATEX**

Approval ID: PxClF07ATEX2708559X

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



## Classifications

### ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

### ETIM

ETIM 9.0	EC001467
----------	----------

### UNSPSC

UNSPSC 21.0	43201500
-------------	----------

# PSI-MOS-RS232/FO1300 E - FO converters

2708588

<https://www.phoenixcontact.com/us/products/2708588>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	79d9c3e3-067f-49ba-ab9e-5448ae9e7261

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)