

2746977

<https://www.phoenixcontact.com/us/products/2746977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Slave protocol chip, for INTERBUS



Commercial data

Item number	2746977
Packing unit	160 pc
Minimum order quantity	160 pc
Sales key	DR14
Product key	DRECAA
GTIN	4017918472788
Weight per piece (including packing)	3.99 g
Weight per piece (excluding packing)	3.252 g
Customs tariff number	85423190
Country of origin	US

IBS SUPI 3 LS - Slave protocol chip



2746977

<https://www.phoenixcontact.com/us/products/2746977>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Protocol chip
Type	TQFP 44

System properties

Module

Internal data length	32-bit internal, external expansion possible
----------------------	--

Electrical properties

IC power supply voltage	5 V DC $\pm 10\%$ (DC)
-------------------------	------------------------

Supply

Typical current consumption	40 mA
-----------------------------	-------

Interfaces

INTERBUS

Connection method	Remote bus/local bus
-------------------	----------------------

Dimensions

Width	12 mm
Depth	12 mm
Length	12 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-40 °C ... 85 °C (at max. 75 % humidity during operation)
Ambient temperature (storage/transport)	5 °C ... 30 °C (at max. 60 %)

IBS SUPI 3 LS - Slave protocol chip



2746977

<https://www.phoenixcontact.com/us/products/2746977>

Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 9.0	EC001601
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IBS SUPI 3 LS - Slave protocol chip



2746977
<https://www.phoenixcontact.com/us/products/2746977>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com