

TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal block with radio interference suppression capacitor between clamping connector and DIN rail, separate ground connection, nominal voltage: 3.3 nF, for mounting on NS 35/7.5, terminal width: 6.2 mm, terminal height: 69 mm

Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Cost-optimized with tailored product features
- No useful signal interference with balanced low-pass

Commercial data

Item number	2798792
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	CL02
Product key	CL2227
GTIN	4017918101480
Weight per piece (including packing)	19.26 g
Weight per piece (excluding packing)	19.26 g
Customs tariff number	85363010
Country of origin	DE

TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Technical data

Product properties

Product type	EMC filters
Type	Single-level terminal block – separate PE connection
Number of positions	1

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	230 V AC
-----------------------	----------

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	6.2 mm
Height	66.5 mm
Depth	69.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-2
Housing material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Protective circuit

Direction of action	Line-Earth Ground
Maximum continuous operating voltage U_C	250 V AC
Rated current	30 A (45 °C)
Protective conductor current I_{PE}	typ. 0.5 mA
Cut-off frequency f_g (3 dB), asym. (PE) in 50 Ω system	typ. 2 MHz
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ω system	typ. 550 kHz (50 Hz)
Cut-off frequency f_g (3 dB), asym. (PE) in 600 Ω system	typ. 170 kHz

TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Capacity (Core-Earth)	typ. 3.3 nF
	Y2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (with end cover)
Ambient temperature (operation)	-20 °C ... 85 °C

Standards and regulations

Standards/specifications	EN 60947-7-1
Note	2009
Standards/specifications	EN 60947-4-2
Note	2009
Standards/specifications	EN 60384-14

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

TT-SLKK 5-C 3N3-230AC - EMC filter


2798792

<https://www.phoenixcontact.com/us/products/2798792>



Drawings

Diagram




TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Circuit diagram



TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Classifications

ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

ETIM

ETIM 9.0	EC000943
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

TT-SLKK 5-C 3N3-230AC - EMC filter

2798792

<https://www.phoenixcontact.com/us/products/2798792>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com