

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in relay interface for protection against interference on the control side, with soldered-in miniature switching relay, contacts (AgNi): medium to large loads, 2 changeover contacts, input voltage 230 V AC

Commercial data

Item number	2826871
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK61B2
GTIN	4017918078027
Weight per piece (including packing)	51.43 g
Weight per piece (excluding packing)	51 g
Country of origin	DE

Technical data

Product properties

Product type	Relay Module
Mechanical service life	> 10 ⁷ cycles
Insulation characteristics	
Overtoltage category	III
Pollution degree	2
Data management status	
Date of last data management	12.09.2025

Electrical properties

Maximum power dissipation for nominal condition	3.45 W
Test voltage (Winding/contact)	1.2 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side	
Nominal input voltage U _N	230 V AC
Input voltage range	207 V AC ... 253 V AC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U _N	approx. 15 mA
Typical response time	approx. 12 ms
Typical release time	approx. 18 ms
Protective circuit	Bridge rectifier; Bridge rectifier
	Surge protection; Varistor
Operating voltage display	Yellow LED
Coil resistance	26590 Ω ±15 %

Output data

Switching	
Contact switching type	2 changeover contacts
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	230 V AC
	250 V DC
Limiting continuous current	5 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC)
	60 W (at 60 V DC)
	40 W (at 110 V DC)
	60 W (at 220 V DC)

ST-REL4-KG230/21-21/SO46 - Relay connectors

2826871

<https://www.phoenixcontact.com/us/products/2826871>



1250 VA (for 250 V AC)

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 40 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	VDE 0110
-----------------------	----------

Mounting

Mounting type	Plug-in mounting
Mounting position	horizontal

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2826871>



EAC

Approval ID: RU*C-DE.*08.B.00010

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 9.0	EC001437
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	cde34f4e-f73c-44a0-a400-46cdea010dc3

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com