

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PT protective connector with protective circuit for a 4-wire floating Ex-i signal circuit. Nominal voltage: 24 V DC

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

Item number	2839253
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL21
Product key	CL2113
GTIN	4017918182878
Weight per piece (including packing)	44.87 g
Weight per piece (excluding packing)	26.15 g
Customs tariff number	85363010
Country of origin	DE

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Technical data

Product properties

Product type	Surge protection for MCR technology
Product family	PLUGTRAB PT
IEC test classification	C1
	C2
	C3
	D1
Type	Male
Number of positions	4
Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC
-----------------------	---------

Connection data

Connection method	Screw connection (in connection with the base element)
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Ex data

Maximum inner capacitance C_i	1.1 nF
Max. internal inductance L_i	1 µH
Max. input current I_i	500 mA (T4 / ≤ 80 °C)
	500 mA (T5 / ≤ 55 °C)
	500 mA (T6 / ≤ 40 °C)
Max. input voltage U_i	30 V DC
max. input power P_i	850.00 mW (T4 / ≤ 80 °C)
	700.00 mW (T5 / ≤ 55 °C)
	700.00 mW (T6 / ≤ 40 °C)
Maximum inner time factor (R_i/L_i)	≤ 10 µs
Ambient temperature (operation)	-40 °C ... 80 °C (T4)
	-40 °C ... 55 °C (T5)
	-40 °C ... 40 °C (T6)

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	44.8 mm
Depth	51.7 mm
Horizontal pitch	1 Div.
Complete module width	17.7 mm
Complete module height	90 mm
Complete module depth	65.5 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & Signal Ground/Shield-Earth Ground
Maximum continuous operating voltage U_C	30 V DC 21 V AC
Rated current	500 mA (40 °C)
Operating effective current I_C at U_C	$\leq 5 \mu A$
Protective conductor current I_{PE}	$\leq 4 \mu A$
Nominal discharge current I_n (8/20) μs (line-line)	308 A
Nominal discharge current I_n (8/20) μs (line-ground)	10 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	1 kA 2 kA (in total)
Total discharge current I_{Total} (8/20) μs	20 kA
Total discharge current I_{Total} (10/350) μs	2 kA
Max. discharge current I_{max} (8/20) μs maximum (line-line)	308 A
Max. discharge current I_{max} (8/20) μs maximum (line-earth)	20 kA (in total)
Nominal pulse current I_{an} (10/1000) μs (line-line)	59 A
Output voltage limitation at 1 kV/ μs (line-line) spike	$\leq 45 V$
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 1 kV$
Output voltage limitation at 1 kV/ μs (line-line) static	$\leq 45 V$

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Output voltage limitation at 1 kV/μs (line-earth) static	≤ 1 kV
Residual voltage at I _n (conductor-conductor)	≤ 70 V
Residual voltage with I _{an} (10/1000) μs (line-line)	≤ 65 V
Voltage protection level U _p (line-line)	≤ 60 V (C1 - 500 V / 250 A)
	≤ 50 V (C3 - 10 A)
	≤ 50 V (C3 - 25 A)
Voltage protection level U _p (line-earth)	≤ 1 kV (C1 - 1 kV / 500 A)
	≤ 1 kV (C2 - 2 kV/1 kA)
	≤ 1 kV (C2 - 10 kV / 5 kA)
	≤ 1 kV (D1 - 1 kA)
Response time t _A (line-line)	≤ 1 ns
Response time t _A (line-earth)	≤ 100 ns
Input attenuation aE, sym.	typ. 0.1 dB (≤ 1 MHz / 50 Ω)
	typ. 0.1 dB (≤ 500 kHz / 150 Ω)
	typ. 0.1 dB (≤ 100 kHz / 600 Ω)
Cut-off frequency f _g (3 dB), sym. in 50 Ω system	typ. 7 MHz
Cut-off frequency f _g (3 dB), sym. in 150 Ω system	typ. 2.5 MHz
Cut-off frequency f _g (3 dB), sym. in 600 Ω system	typ. 600 kHz
Resistance per path	0 Ω
Surge protection fault message	none
Max. required back-up fuse	500 mA (T)
Impulse durability (line-line)	C1 - 0.5 kV / 250 A
	C3 - 10 A
	C3 - 25 A
Impulse durability (line-earth)	C1 - 1 kV / 500 A
	C2 - 2 kV / 1 kA
	C2 - 10 kV / 5 kA
	D1 - 1 kA
Alternating current carrying capacity (line-earth)	5 A - 1 s

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (amsl)

Approvals

Conformity/Approvals

ATEX	Ex II 1G Ex ia IIC T4...T6 Ga
	Ex II 1D Ex ia IIIC T135 °C...T85 °C Da
IECEX	Ex ia IIC T4...T6 Ga
	Ex ia IIIC T135 °C...T85 °C Da

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Standards and regulations

Standards/specifications	EN 61643-21
Note	A2:2013
Standards/specifications	EN 60079-0
Note	2018
Standards/specifications	EN 60079-11
Note	2012
Standards/specifications	IEC 61643-21
Note	A2:2012
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-11
Note	2011
Standards/specifications	GB/T 3836.1
Note	2021
Standards/specifications	GB/T 3836.4
Note	2021

Mounting

Mounting type	on base element
---------------	-----------------

PT 4-EX(I)-24DC-ST - Surge protection plug


2839253

<https://www.phoenixcontact.com/us/products/2839253>




Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Diagram




PT 4-EX(I)-24DC-ST - Surge protection plug

2839253

<https://www.phoenixcontact.com/us/products/2839253>



Circuit diagram



PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2839253>



DNV GL

Approval ID: TAE00001N6



ATEX

Approval ID: KEMA 00ATEX1099 X



IECEx

Approval ID: IECEx KEM 10.0063X

INMETRO

Approval ID: DNV 19.0031 X/01



NEPSI-EX

Approval ID: GYJ20.1177X



UKCA-EX

Approval ID: DEKRA 21UKEX0234 X

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Classifications

ECLASS

ECLASS-13.0	27171502
ECLASS-15.0	27171502

ETIM

ETIM 9.0	EC001625
----------	----------

UNSPSC

UNSPSC 21.0	39121620
-------------	----------

PT 4-EX(I)-24DC-ST - Surge protection plug



2839253

<https://www.phoenixcontact.com/us/products/2839253>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ee3ed19a-1f52-414c-81bf-f64a1e7caf37

EF3.0 Climate Change

CO2e kg	1.021 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com