

FL MC 1000 ST - FO converters

2891321

<https://www.phoenixcontact.com/us/products/2891321>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO converter with ST fiber optic connection (1300 nm), for converting 100Base-TX to multi-mode fiberglass. Auto MDI(X) function and comprehensive link diagnostics. DIN rail mountable.

Product description

The FL MC 1000 ST media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an ST connector.

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring

Commercial data

Item number	2891321
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC312
GTIN	4046356869621
Weight per piece (including packing)	281.3 g
Weight per piece (excluding packing)	278 g
Customs tariff number	85176200
Country of origin	TW

FL MC 1000 ST - FO converters

2891321

<https://www.phoenixcontact.com/us/products/2891321>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Media converter
MTTF	95.85 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
Signal delay	± 1.3 µs (Store and Forward mode, 10/100 Mbps, depending on the frame size)

Electrical properties

Electrical isolation	VCC // FE // Ethernet
Test voltage data interface/power supply	1500 V AC (500 V AC, 1 minute)

Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	73 mA (24 V DC)

Connection data

Supply

Connection method	Plug-in/screw connection via COMBICON
-------------------	---------------------------------------

Interfaces

Signal	Ethernet
--------	----------

Data: optical FO

Transmit capacity, minimum	-19 dBm
Transmit capacity, maximum	-14 dBm
Transmission length incl. 3 dB system reserve	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000) 3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600) 9.6 km (fiberglass with F-G 50/125 0.7 dB/km F1200) 5.3 km (fiberglass with F-G 50/125 1.6 dB/km F800)
Connection method	ST
Wavelength	1310 nm

FL MC 1000 ST - FO converters

2891321

<https://www.phoenixcontact.com/us/products/2891321>



Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LINK/ACT, 100
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

Mechanical tests

Vibration (operation) in accordance with IEC 60068-2-6:1982	: Operation: 5g, 150 Hz, criterion A
Shock in accordance with IEC 60068-2-27:1997	: 30g, 11 ms period, half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	0 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Approvals

Conformity/Approvals	
Conformance	CE-compliant
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Mounting

Mounting type	DIN rail: 35 mm
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715

FL MC 1000 ST - FO converters

2891321

<https://www.phoenixcontact.com/us/products/2891321>



Classifications

ECLASS

ECLASS-13.0	19170411
-------------	----------

ETIM

ETIM 9.0	EC001467
----------	----------

UNSPSC

UNSPSC 21.0	43201500
-------------	----------

FL MC 1000 ST - FO converters

2891321

<https://www.phoenixcontact.com/us/products/2891321>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com