

TP-NEF/20 - Line filters



2901986

<https://www.phoenixcontact.com/us/products/2901986>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Secondary mains filter, with push-in spring-cage connection, for mounting on NS 35/7,5 or NS 32

Commercial data

Item number	2901986
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMPQZY
GTIN	4046356641920
Weight per piece (including packing)	680.7 g
Weight per piece (excluding packing)	68.3 g
Country of origin	DE

TP-NEF/20 - Line filters

2901986

<https://www.phoenixcontact.com/us/products/2901986>



Technical data

Product properties

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC
Max. total current of voltage supply	26 A
Rated insulation voltage	50 V
Rated surge voltage	2.5 kV (Basic insulation)

Connection data

Input

Connection method	Push-in connection
Number of positions	3
Conductor cross-section rigid	0.2 mm ² ... 10 mm ²
Conductor cross-section flexible	0.2 mm ² ... 6 mm ²
Conductor cross-section AWG	24 ... 8

Output

Connection method	Push-in connection
Number of positions	3
Conductor cross-section rigid	0.2 mm ² ... 10 mm ²
Conductor cross-section flexible	0.2 mm ² ... 6 mm ²
Conductor cross-section AWG	24 ... 8

Dimensions

Item dimensions

Width	40 mm
Height	115 mm
Depth	130 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

TP-NEF/20 - Line filters

2901986

<https://www.phoenixcontact.com/us/products/2901986>



Mounting position

any

TP-NEF/20 - Line filters

2901986

<https://www.phoenixcontact.com/us/products/2901986>



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-25
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com