

CABLE-D15SUB/S/S/ 720/KONFEK/S - Cable



2902259

<https://www.phoenixcontact.com/us/products/2902259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled, shielded round cable, with two 15-pos. D-SUB pin strips (1:1 connection), cable length: 7.20 m



Your advantages

- 15-pos.

Commercial data

Item number	2902259
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	DK2AZZ
GTIN	4046356649919
Weight per piece (including packing)	786.2 g
Weight per piece (excluding packing)	768.2 g
Country of origin	DE

CABLE-D15SUB/S/S/ 720/KONFEK/S - Cable



2902259

<https://www.phoenixcontact.com/us/products/2902259>

Technical data

Product properties

Product type	System cable
Insulation characteristics: Air clearances and creepage distances	
Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Nominal operating mode	100% operating factor
Max. current carrying capacity per path	2 A (uncoiled)

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV

Cable/line

Cable length	7.2 m
15X0.25 [PVC]	
UL AWM Style	2464/1061
Number of positions	15
Shielded	yes
Cable type	15X0.25 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	15x 0.25 mm ²
Wire diameter incl. insulation	1.2 mm ±0.05 mm
External cable diameter	7.90 mm ±0.5 mm
Outer sheath, material	Semi-rigid PVC

CABLE-D15SUB/S/S/ 720/KONFEK/S - Cable

2902259

<https://www.phoenixcontact.com/us/products/2902259>



External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	$\leq 80 \Omega/\text{km}$ (at 20 °C)
Insulation resistance	$\geq 20 \text{ M}\Omega\text{-km}$ (at 20 °C)
Smallest bending radius, fixed installation	67 mm
Smallest bending radius, movable installation	126 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of $\geq 15x$ outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Connection data

Field level

Connection in acc. with standard	DIN 41652/IEC 60807-2
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	15
Insertion/withdrawal cycles	> 200

Controller level

Connection in acc. with standard	DIN 41652/IEC 60807-2
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	15
Insertion/withdrawal cycles	> 200

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

CABLE-D15SUB/S/S/ 720/KONFEK/S - Cable




2902259

<https://www.phoenixcontact.com/us/products/2902259>

Drawings

Diagram



Maximum permissible current per path in uncoiled state

CABLE-D15SUB/S/S/ 720/KONFEK/S - Cable

2902259

<https://www.phoenixcontact.com/us/products/2902259>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com