

# UM-BASIC/PRO PCB S-LOCK KMGY - Locking



2202031

<https://www.phoenixcontact.com/us/products/2202031>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Locking element for locking the upper PCB onto UM-BASIC/PRO housings close to the edge



## Your advantages

- Different base profiles, each with three PCB levels
- Module covers of different geometries can be positioned in any way
- Compatibility with many standard connection technologies
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

## Commercial data

Item number	2202031
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AC17
Product key	ACHDAZ
GTIN	4055626005423
Weight per piece (including packing)	0.318 g
Weight per piece (excluding packing)	0.3 g
Customs tariff number	39269097
Country of origin	DE

# UM-BASIC/PRO PCB S-LOCK KMGY - Locking



2202031

<https://www.phoenixcontact.com/us/products/2202031>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Mounting material
Housing type	Press-drawn section housings
Housing series	UM-BASIC
Product family	UM-PRO

### Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

### Environmental and real-life conditions

Glow-wire test	
Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test	
Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel	
Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# UM-BASIC/PRO PCB S-LOCK KMGY - Locking

2202031

<https://www.phoenixcontact.com/us/products/2202031>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202031>



**UL Recognized**  
Approval ID: E240868

# UM-BASIC/PRO PCB S-LOCK KMGY - Locking

2202031

<https://www.phoenixcontact.com/us/products/2202031>



## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-BASIC/PRO PCB S-LOCK KMGY - Locking

2202031

<https://www.phoenixcontact.com/us/products/2202031>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)