

EMD-BL-PH-480 - Monitoring relay



2903527

<https://www.phoenixcontact.com/us/products/2903527>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monitoring relay for monitoring the phase sequence and asymmetry of 3-phase voltages at 208 .. . 480 V AC / 120 ... 277 V AC, configurable asymmetry, 1 changeover contact, with screw connection

Product description

Safety and system availability requirements are constantly on the increase – across all industries. Processes are becoming more and more complex, not only in machine building and the chemical industry but also in building technology. The demands placed on energy technology are also constantly on the rise.

It is only by continuously monitoring key network and system parameters that error-free and therefore cost-effective operation can be achieved. Electronic monitoring relays from the EMD series are available for a wide range of monitoring tasks so that the consequences of errors can be avoided or kept within limits.

The operating states are signaled via color LEDs and any errors that occur can be sent to a controller via a floating contact or can shut down a section of the system. All device versions are equipped with response delays so that measured values outside the set monitoring range can be briefly tolerated.

Commercial data

Item number	2903527
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK6481
GTIN	4046356747233
Weight per piece (including packing)	81.5 g
Weight per piece (excluding packing)	80 g
Customs tariff number	85364900
Country of origin	AT

EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Technical data

Product properties

Product type	Phase monitoring relay
Operating mode	100% operating factor
Mechanical service life	15x 10 ⁶ cycles

Insulation characteristics

Insulation	Basic insulation
Oversupply category	III
Pollution degree	2

Electrical properties

Service life electrical	1x 10 ⁵ cycles
Mains type	3-phase
Rated insulation voltage	519 V (Supply circuit) 250 V (Output circuit)
Rated surge voltage	4 kV

Supply

Supply voltage	±10 % (= measuring voltage)
Supply voltage range	±10 % (= measuring voltage)
Nominal power consumption	10 VA ((1 W) at 400 V/50 Hz) 16 VA ((1.5 W) at 480 V/60 Hz)

Input data

Input name	Measuring input
Measured value	AC sine (48 Hz ... 63 Hz)
Nominal input voltage U _N	480 V (3~ 208 ... 480 V / 120 ... 277 V)
Frequency range	48 Hz ... 63 Hz
Setting range for response delay	0.1 s ... 10 s
Min setting range of the voltage threshold value	187 V AC
Max. setting range of the voltage threshold value	519 V AC
Function	Phase sequence Phase failure Asymmetry
Basic accuracy	≤ 5 % (of scale end value)
Setting accuracy	± 5 % (of scale end value)
Repeat accuracy	≤ 2 %
Asymmetry	5 % ... 25% / OFF
Recovery time	> 500 ms

Output data

Switching

EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Contact switching type	1 floating changeover contact
Maximum switching voltage	250 V AC (in acc. with IEC 60664-1)
Interrupting rating (ohmic load) max.	1250 VA (5 A / 250 V AC)
Output fuse	5 A (fast-blow)

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 14
Tightening torque	1 Nm ... 1 Nm

Signaling

Status display	LED (yellow)
Operating voltage display	Green LED
Error indication	Red LED

Dimensions

Width	17.5 mm
Height	89.5 mm
Depth	65.5 mm

Material specifications

Color	gray (RAL 7042)
Housing insulation material	Polyamide PA 6.6, self-extinguishing

Environmental and real-life conditions

Ambient conditions	
Degree of protection (Housing)	IP40 (Housing)
Degree of protection (Connection terminal blocks)	IP20 (Connection terminal blocks)
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Climatic class	3K3 (in acc. with EN 60721)
Permissible humidity (operation)	15 % ... 85 %

Approvals

CE	
Certificate	CE-compliant
UL, USA/Canada	
Identification	UL/C-UL Listed UL 508

EMC data

EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2

Noise emission	
Standards/regulations	EN 61000-6-3

Standards and regulations

Standards/regulations	DIN EN 60947-5-1
-----------------------	------------------

Mounting

Mounting type	DIN rail mounting
Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any

EMD-BL-PH-480 - Monitoring relay




2903527

<https://www.phoenixcontact.com/us/products/2903527>

Drawings

Block diagram



EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903527>



EAC

Approval ID: RU*C-DE.*08.B.00010



UL Listed

Approval ID: FILE E 172140



cUL Listed

Approval ID: FILE E 172140

EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Classifications

ECLASS

ECLASS-13.0	27371803
ECLASS-15.0	27371803

ETIM

ETIM 9.0	EC001441
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

EMD-BL-PH-480 - Monitoring relay

2903527

<https://www.phoenixcontact.com/us/products/2903527>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com