

ST-OV3-120AC/ 60DC/3 - Solid-state relay



2903613

<https://www.phoenixcontact.com/us/products/2903613>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in power solid-state relay, with LED and protective circuit in input and output circuits, input: 120 V AC, output: 12 - 60 V DC/max. 3 A, can be plugged into basic terminal blocks

Commercial data

Item number	2903613
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61B2
GTIN	4017918079062
Weight per piece (including packing)	30.8 g
Weight per piece (excluding packing)	30.8 g
Customs tariff number	85364900
Country of origin	DE

ST-OV3-120AC/ 60DC/3 - Solid-state relay



2903613

<https://www.phoenixcontact.com/us/products/2903613>

Technical data

Product properties

Product type	Single solid-state relay
Data management status	
Date of last data management	05.09.2025

Electrical properties

Test voltage (Input/output)	2.5 kV AC (Input/output)
-----------------------------	--------------------------

Input data

Nominal input voltage U_N	120 V AC
Input voltage range in reference to U_N	0.8 ... 1.2
Input voltage range	96 V AC ... 144 V AC
Switching threshold "0" signal in reference to U_N	≤ 0.4
Switching threshold "1" signal in reference to U_N	≥ 0.8
Typical input current at U_N	4 mA
Typical response time	3 ms
Typical turn-off time	13 ms
Transmission frequency	10 Hz

Output data

Design of digital output	electronic
Output voltage range	12 V DC ... 60 V DC
Limiting continuous current	3 A (see derating curve)
Surge current	5 A ($t = 1$ s)
Peak offstate voltage	70 V DC (Collector-emitter reverse voltage)
Voltage drop at max. limiting continuous current	1.2 V
Output circuit	2-conductor, floating
Protective circuit	Reverse polarity protection; Polarity protection diode Surge protection

Dimensions

Width	20.8 mm
Height	33 mm
Depth	66.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
---------------------------------	------------------

ST-OV3-120AC/ 60DC/3 - Solid-state relay



2903613

<https://www.phoenixcontact.com/us/products/2903613>

Ambient temperature (storage/transport)	-20 °C ... 70 °C
---	------------------

Standards and regulations


Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110

Mounting

Mounting position	any
-------------------	-----

Drawings

Diagram



- ① In rows with zero spacing
- ② stand-alone device

ST-OV3-120AC/ 60DC/3 - Solid-state relay

2903613

<https://www.phoenixcontact.com/us/products/2903613>



Circuit diagram




ST-OV3-120AC/ 60DC/3 - Solid-state relay

2903613

<https://www.phoenixcontact.com/us/products/2903613>



Circuit diagram



ST-OV3-120AC/ 60DC/3 - Solid-state relay



2903613

<https://www.phoenixcontact.com/us/products/2903613>

Classifications

UNSPSC

UNSPSC 21.0	39122326
-------------	----------

ST-OV3-120AC/ 60DC/3 - Solid-state relay



2903613

<https://www.phoenixcontact.com/us/products/2903613>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com