

ME TBUS PST 1,5/ 5-3,81 - Contact strip




2279033

<https://www.phoenixcontact.com/us/products/2279033>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pin strip for soldering into the PCB, for contacting in DIN rail bus connectors



Your advantages

- Space-saving installation under the housing in the DIN rail
- Contact design enables electronics modules to be easily snapped on
- Power supply and communication without additional wiring

Commercial data

Item number	2279033
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC08
Product key	ACHACZ
GTIN	4046356180573
Weight per piece (including packing)	1.12 g
Weight per piece (excluding packing)	1.054 g
Customs tariff number	85366990
Country of origin	DE

ME TBUS PST 1,5/ 5-3,81 - Contact strip



2279033

<https://www.phoenixcontact.com/us/products/2279033>

Technical data

Product properties

Product type	Pin strip
Number of positions	5
Pitch	3.81 mm
Pin layout	Linear pinning
Solder pins per potential	1

Electrical properties

Properties

Nominal current I_N	6 A
Nominal voltage U_N	125 V
Contact resistance	2.34 mΩ
Rated voltage (III/3)	125 V
Rated surge voltage (III/3)	2.5 kV
Rated voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV

Mounting

Mounting type	Wave soldering
Pin layout	Linear pinning

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	gold-plated

Material data - housing

Color (Housing)	black (9005)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

Notes

Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)
----------------	---

Dimensions

ME TBUS PST 1,5/ 5-3,81 - Contact strip



2279033

<https://www.phoenixcontact.com/us/products/2279033>

Pitch	3.81 mm
Width [w]	10.8 mm
Solder pin length [P]	2.05 mm
Pin dimensions	0.6 x 0.6 mm

Mechanical tests

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
Result	Test passed

Insertion and withdrawal forces

Result	Test passed
No. of cycles	25
Insertion strength per pos. approx.	2.18 N
Withdraw strength per pos. approx.	1.38 N

Polarization and coding

Specification	IEC 60512-13-5:2006-02
Result	Test passed

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-1:2002-02
Tested number of positions	5

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Insulating material group	I
Rated insulation voltage (III/3)	125 V
Rated surge voltage (III/3)	2.5 kV
minimum clearance value - non-homogenous field (III/3)	1.5 mm
minimum creepage distance (III/3)	1.9 mm
Rated insulation voltage (III/2)	125 V
Rated surge voltage (III/2)	2.5 kV
minimum clearance value - non-homogenous field (III/2)	1.5 mm
minimum creepage distance (III/2)	1.5 mm

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz

ME TBUS PST 1,5/ 5-3,81 - Contact strip



2279033

<https://www.phoenixcontact.com/us/products/2279033>

Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis (pos. and neg.)

Durability test

Specification	IEC 60512-9-1:2010-03
Impulse withstand voltage at sea level	2.5 kV
Contact resistance R_1	2.34 mΩ
Contact resistance R_2	2.27 mΩ
Insertion/withdrawal cycles	25

Climatic test

Specification	DIN 50018:2013-05
Corrosive stress	0.2 dm ³ SO ₂ on 300 dm ³ /40 °C/1 cycle
Thermal stress	100 °C/168 h
Power-frequency withstand voltage	1.39 kV

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	30g
Shock duration	18 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------


ME TBUS PST 1,5/ 5-3,81 - Contact strip

2279033

<https://www.phoenixcontact.com/us/products/2279033>



Drawings



Type: ME TBUS PST 1,5/ 5-3,81 ...

ME TBUS PST 1,5/ 5-3,81 - Contact strip



2279033

<https://www.phoenixcontact.com/us/products/2279033>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ME TBUS PST 1,5/ 5-3,81 - Contact strip



2279033

<https://www.phoenixcontact.com/us/products/2279033>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com