


# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with push-in connections and high density D-SUB miniature male connector, for mounting on NS 35 rails, no. of pos.: 44

## Commercial data

Item number	2904270
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2122
GTIN	4046356814799
Weight per piece (including packing)	216.1 g
Weight per piece (excluding packing)	214.6 g
Customs tariff number	85366990
Country of origin	US

# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	44

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated surge voltage	1.2 kV

### Connection data

#### Connection 1 (control level)

Connection method	High density D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	44

#### Connection 2 (field level)

Connection method	Push-in connection
Stripping length	8 mm
Number of positions	45
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

Width	82.5 mm
Height	75.8 mm
Depth	63 mm

### Material specifications

Color	gray (RAL 7042)
-------	-----------------

# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# VIP-3/PT/HD44SUB/M - Termination board


2904270

<https://www.phoenixcontact.com/us/products/2904270>




## Drawings

Dimensional drawing



Circuit diagram



Universal circuit diagram

# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904270>

		CSA		
		Approval ID: 2122203		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine		105 V	1 A	26 - 14
				-

		cUL Recognized		
		Approval ID: E238705		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine		125 V	1 A	26 - 14
				-

		UL Recognized		
		Approval ID: E238705		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine		125 V	1 A	26 - 14
				-

		CSAus		
		Approval ID: 2122203		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine		105 V	1 A	28 - 14
				-

# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VIP-3/PT/HD44SUB/M - Termination board

2904270

<https://www.phoenixcontact.com/us/products/2904270>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0efdc639-c9d1-4eb8-9058-7972eb48dfcd

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)