

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE front adapter, for Siemens SIMATIC® S7-400, 1x 32 channels can be connected



Your advantages

- Transmission of a maximum of 32 digital channels via a 50-pos. system cable

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2294500 |
| Packing unit | 2 pc |
| Minimum order quantity | 2 pc |
| Sales key | C421 |
| Product key | DK231S |
| GTIN | 4017918129750 |
| Weight per piece (including packing) | 198.855 g |
| Weight per piece (excluding packing) | 198.47 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



Technical data

Product properties

| | |
|----------------|---------------|
| Product type | Front adapter |
| Product family | VARIOFACE |

Insulation characteristics: Air clearances and creepage distances

| | |
|---------------------|-----------------------|
| Insulation | Functional insulation |
| Oversupply category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|-----------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (per branch) | ≤ 1 A |
| Current (Voltage supply via IDC/FLK) | ≤ 2 A |
| Current (Voltage supply via spade connection) | ≤ 8 A |

Air clearances and creepage distances

| | |
|--------------------------|--------------------|
| Rated insulation voltage | 63 V |
| Rated surge voltage | 0.6 kV (1.2/50 µs) |

Supported controller SIEMENS S7-400

| | |
|-------------------|--------------------|
| Suitable I/O card | 6ES7421-1BL01-0AA0 |
| | 6ES7422-1BL00-0AA0 |
| | 6ES7422-7BL00-0AB0 |

Supported controller SIEMENS S7-400

| | |
|-------------------|--|
| Note | Only in conjunction with VIP-2/SC/FLK50/S7/A-S400, Item No. 2322359 VIP-2/PT/FLK50/S7/A-S400, Item No. 2904289 all DR wire bridges on the adapter must be disconnected. |
| Suitable I/O card | 6ES7421-7BH01-0AB0 |
| | 6ES7421-7DH00-0AA0 |

Connection data

Connection 1 (control level)

| | |
|---------------------|--------------------|
| Connection method | Plug-in connection |
| Number of positions | 48 |

Connection 2 (field level)

| | |
|----------------------------------|-------------------|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 50 |

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



| | |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 3 (supply)

| | |
|---------------------|------------------|
| Connection method | Spade connection |
| Number of positions | 5 |
| Note | 2,8 x 0,8 |

Dimensions

Item dimensions

| | |
|--------|----------|
| Width | 24.2 mm |
| Height | 273.5 mm |
| Depth | 67.6 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|------------------|
| Degree of protection (Module) | IP00 |
| Degree of protection (Installation location) | ≥ IP54 |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Altitude | ≤ 2000 m |

Standards and regulations

Air clearances and creepage distances

| | |
|-----------------------|----------------|
| Standards/regulations | EN IEC 60664-1 |
|-----------------------|----------------|

Mounting

| | |
|-------------------|------------------|
| Mounting type | Plug-in mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
| Notes on operation | For I/O cards 6ES7 421-1BL01-0AA0, 6ES7 422-1BL00-0AA0, and 6ES7 422-7BL00-0AB0: Thanks to the wire bridges that are supplied as standard, the input and output bytes are non-isolated. |
| Notes on operation | For I/O cards 6ES7 421-7BH01-0AB0 and 6ES7 421-7DH00-0AB0: Only operate in conjunction with VIP-2/SC/FLK50/S7/A-S400 (Item No. 2322359) or VIP-2/PT/FLK50/S7/A-S400 (Item No. 2904289). All wire bridges on the adapter must be disconnected. |


FLKM 50-PA-S400 - Front adapter



2294500

<https://www.phoenixcontact.com/us/products/2294500>

Drawings



Connection scheme FLKM 50-PA-S400

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2294500>

| cUL Recognized | | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|----------------|--|-----------------------|-----------------------|-------------------|----------------------|
| keine | | 125 V | 0.5 A | - | - |

| UL Recognized | | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|---------------|--|-----------------------|-----------------------|-------------------|----------------------|
| keine | | 125 V | 0.5 A | - | - |

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242292 |
| ECLASS-15.0 | 27242292 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002584 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

FLKM 50-PA-S400 - Front adapter

2294500

<https://www.phoenixcontact.com/us/products/2294500>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com