

FLKMS-D37 SUB/B/ZFK3DS/PE - Termination board

2295952

<https://www.phoenixcontact.com/us/products/2295952>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with spring-cage connection and D-Subminiature socket strip, for mounting on NS 35/7.5 or NS 32, 37-pos.

Commercial data

Item number	2295952
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2A82
GTIN	4017918448035
Weight per piece (including packing)	196.3 g
Weight per piece (excluding packing)	137.32 g
Customs tariff number	85369010
Country of origin	DE

FLKMS-D37 SUB/B/ZFK3DS/PE - Termination board

2295952

<https://www.phoenixcontact.com/us/products/2295952>



Technical data

Product properties

Product type	Interface module
Number of positions	37

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overtoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2.5 A

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 µs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Insertion/withdrawal cycles	> 500
Pitch	2.77 mm

Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7.5 mm
Number of positions	39
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
	0.2 mm ² ... 1.5 mm ²
	0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve)
Conductor cross-section flexible (2 conductors with same cross section)	0.25 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 14
Pitch	5.08 mm

Signaling

Status display present	no
------------------------	----

FLKMS-D37 SUB/B/ZFK3DS/PE - Termination board

2295952

<https://www.phoenixcontact.com/us/products/2295952>



Dimensions

Item dimensions

Width	75 mm
Height	90 mm
Depth	70 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKMS-D37 SUB/B/ZFK3DS/PE - Termination board

2295952

<https://www.phoenixcontact.com/us/products/2295952>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2295952>

cUL Recognized		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	2 A	-	-

UL Recognized		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	2 A	-	-

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKMS-D37 SUB/B/ZFK3DS/PE - Termination board

2295952

<https://www.phoenixcontact.com/us/products/2295952>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com