

VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 26-pos.

Your advantages

- 10-pos. ... 64-pos.
- Metal foot
- In accordance with IEC 60603-13
- 1:1 connection
- Screw connection

Commercial data

Item number	2315052
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2111
GTIN	4046356312882
Weight per piece (including packing)	127 g
Weight per piece (excluding packing)	143 g
Customs tariff number	85366990
Country of origin	US

VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	26
No. of channels	26

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated surge voltage	0.6 kV

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	26
Pitch	2.54 mm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	57.1 mm
Height	69 mm
Depth	62 mm

VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-3/SC/FLK26 - Termination board


2315052

<https://www.phoenixcontact.com/us/products/2315052>



Drawings

Circuit diagram



VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2315052>

		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	1 A	30 - 12	-

		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	1 A	30 - 12	-

		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	1 A	30 - 12	-

		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		125 V	1 A	30 - 12	-

VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/SC/FLK26 - Termination board

2315052

<https://www.phoenixcontact.com/us/products/2315052>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com