

UM-2KS50/16DI/RS/SO225 - Input module



2319812

<https://www.phoenixcontact.com/us/products/2319812>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

16-channel digital input module with screw connection and redundant voltage supply. Suitable for Yokogawa SDV 144 card.



Commercial data

Item number	2319812
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK2A8N
GTIN	4046356440349
Weight per piece (including packing)	584.4 g
Weight per piece (excluding packing)	333.33 g
Country of origin	DE

UM-2KS50/16DI/RS/SO225 - Input module

2319812

<https://www.phoenixcontact.com/us/products/2319812>



Technical data

Product properties

Product type	Interface module
No. of channels	16

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Oversupply voltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	30 V DC
Max. current carrying capacity per branch	100 mA
Max. total current of all branches	2 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μ s)

Supported controller YOKOGAWA ProSafe-RS

Suitable I/O card	SDV144
-------------------	--------

Connection data

Field level

Connection method	Screw connection
Number of positions	48
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Tightening torque	0.5 Nm

Supply

Connection method	Screw connection
Number of connections	1
Number of positions	6
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Signaling

Status display present	yes
------------------------	-----

Dimensions

Item dimensions

Width	250 mm
Height	125.4 mm
Depth	75.6 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 55 °C
Altitude	< 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UM-2KS50/16DI/RS/SO225 - Input module

2319812

<https://www.phoenixcontact.com/us/products/2319812>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2319812>



EAC

Approval ID: RU*-DE.*08.B.01829*

UM-2KS50/16DI/RS/SO225 - Input module

2319812

<https://www.phoenixcontact.com/us/products/2319812>



Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	66cefa93-a642-47a1-9285-8dae10c6ef29

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com