

REL-MR-BL-200AC/21-21/MS - Single relay



2908182

<https://www.phoenixcontact.com/us/products/2908182>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in miniature relay, with power contact, 2 changeover contacts, test button, mechanical switch position indicator, polarity: bipolar, input voltage: 200 V AC

Commercial data

Item number	2908182
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6195
GTIN	4055626279411
Weight per piece (including packing)	17.64 g
Weight per piece (excluding packing)	17.64 g
Customs tariff number	85364190
Country of origin	CN

REL-MR-BL-200AC/21-21/MS - Single relay



2908182

<https://www.phoenixcontact.com/us/products/2908182>

Technical data

Product properties

Product type	Single relay
Operating mode	100% operating factor
Mechanical service life	5x 10 ⁶ cycles

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	05.09.2025
------------------------------	------------

Electrical properties

Service life electrical	see diagram
Maximum power dissipation for nominal condition	0.8 W
Test voltage (Winding/contact)	5 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (Changeover contact/changeover contact)	2.5 kV AC (50 Hz, 1 min., changeover contact/changeover contact)
Rated insulation voltage	250 V AC

Input data

Coil side

Nominal input voltage U _N	200 V AC
Input voltage range	160 V AC ... 270 V AC
Input voltage range in reference to U _N	0.8 ... 1.35 (see diagram)
Mains frequency	50/60 Hz
Drive and function	monostable
Typical input current at U _N	4 mA
Typical response time	3 ms ... 12 ms (depending on phase relation)
Typical release time range	2 ms ... 8 ms (depending on phase relation)
Status display	LED (yellow)

Output data

Switching

Contact switching type	2 changeover contacts
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V (at 10 mA)
Limiting continuous current	8 A
Maximum inrush current	16 A (20 ms)
Min. switching current	10 mA (at 12 V)

REL-MR-BL-200AC/21-21/MS - Single relay



2908182

<https://www.phoenixcontact.com/us/products/2908182>

Interrupting rating (ohmic load) max.	192 W (at 24 V DC)
	62 W (at 48 V DC)
	42 W (at 60 V DC)
	55 W (at 110 V DC)
	66 W (at 220 V DC)

Connection data

Connection method	Solder connection
-------------------	-------------------

Dimensions

Width	13 mm
Height	29 mm
Depth	25.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	RT II
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C


Standards and regulations

Standards/regulations	IEC 61810
	IEC 60664


Mounting

Mounting position	any
-------------------	-----


Drawings



Operating voltage range



Interrupting rating




Electrical service life

Diagram



Service life reduction factor with various cos phi

Circuit diagram



REL-MR-BL-200AC/21-21/MS - Single relay



2908182

<https://www.phoenixcontact.com/us/products/2908182>

Classifications

ETIM

ETIM 8.0	EC001437
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

REL-MR-BL-200AC/21-21/MS - Single relay



2908182

<https://www.phoenixcontact.com/us/products/2908182>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com