

ME MF 17,5 - Base latch

2908281

<https://www.phoenixcontact.com/us/products/2908281>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Metal foot catch with spring, for intermediate elements.



Your advantages

- Easy installation

Commercial data

Item number	2908281
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC08
Product key	ACHAAZ
GTIN	4017918167882
Weight per piece (including packing)	4.042 g
Weight per piece (excluding packing)	4.004 g
Customs tariff number	73269098
Country of origin	DE

ME MF 17,5 - Base latch

2908281

<https://www.phoenixcontact.com/us/products/2908281>



Technical data

Product properties

Product type	Base latches
Housing type	DIN rail housing
Housing series	ME
Product family	ME 17,5..

Dimensions

Width	17.5 mm
Height	30 mm
Depth	6.5 mm

Material specifications

Material	Steel (tin-plated)
----------	--------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

ME MF 17,5 - Base latch

2908281

<https://www.phoenixcontact.com/us/products/2908281>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MF 17,5 - Base latch

2908281

<https://www.phoenixcontact.com/us/products/2908281>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com