

TP090ATW/107020000 S00093 - Touch panel



2401624

<https://www.phoenixcontact.com/us/products/2401624>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 22.9 cm / 9"-TFT display (analog resistive (polyester)), 800 x 480 pixel(s) (WVGA), 65536 colors, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, CODESYS, without bus system.

Commercial data

Item number	2401624
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABZ
GTIN	4055626292861
Weight per piece (including packing)	1,300 g
Weight per piece (excluding packing)	1,300 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	64 MB SDRAM
	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	22.9 cm / 9"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	800 cd/m², typical (adjustable)
MTBF	70000 h
Color spectrum	65536 colors
Reading angle left	85.00 °
Reading angle right	85.00 °
Reading angle top	85.00 °
Reading angle bottom	85.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	CODESYS
---------------	---------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
Max. current consumption	0.7 A

Real-time clock

Realtime clock	Yes
----------------	-----

Mounting

Mounting type	Front mounting
---------------	----------------

TP090ATW/107020000 S00093 - Touch panel



2401624

<https://www.phoenixcontact.com/us/products/2401624>

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	260 mm / 172 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	252 mm / 164 mm / 66 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com