

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Output loop-powered temperature transducer for transmitting up to 2 sensor signals from RTD and TC sensors, as well as from resistance and voltage sensors via 4 mA ... 20 mA. HART, Signal conditioners with SIL functional safety, Standard configuration, Safety Integrity Level (SIL, IEC 61508): 2, Systematic Capability: 3, Screw connection

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2908662 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C401 |
| Product key | DK1143 |
| GTIN | 4055626355450 |
| Weight per piece (including packing) | 201.7 g |
| Weight per piece (excluding packing) | 171.8 g |
| Customs tariff number | 85437090 |
| Country of origin | DE |

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Technical data

Product properties

| | |
|-----------------|-------------------------|
| Product type | Temperature transmitter |
| Product family | MACX Analog |
| No. of channels | 2 |
| Configuration | Software |
| | HART |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

System properties

Functionality

| | |
|---------------|----------|
| Configuration | Software |
| | HART |

Electrical properties

| | |
|---|------------|
| Electrical isolation between input and output | yes |
| Step response (0–99%) | 0.8 s (TC) |

Electrical isolation Input/output

| | |
|--------------|-----------------------|
| Test voltage | 2 kV AC (50 Hz, 60 s) |
|--------------|-----------------------|

Supply

| | |
|----------------------|--|
| Supply voltage range | loop-powered, no external supply necessary |
| | 12 V DC ... 42 V DC (Standard) |
| | 12 V DC ... 32 V DC (SIL active) |

Input data

Signal

| | |
|--------------|-------------|
| Input signal | Temperature |
|--------------|-------------|

Measurement

| | |
|-------------------------------------|--|
| Number of inputs | 2 |
| Input voltage range | -20 mV ... 100 mV (Minimum measuring span: 5 mV) |
| Sensor types (RTD) that can be used | Pt, Ni, Cu sensors: 2, 3, 4-wire |
| Sensor types that can be used (TC) | A, B, C, D, E, J, K, L, N, R, S, T, U |
| Temperature measuring range | -250 °C ... 2500 °C (Range depending on the sensor type) |
| | -200 °C ... 850 °C (Pt 100) |
| Temperature measuring range | > 10 K (RTD) |
| | > 50 K (TC) |
| Linear resistance measuring range | 10 Ω ... 2000 Ω (Minimum measuring span: 10 Ω) |

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Output data

Signal: Current

| | |
|----------------------------|--|
| Configurable/programmable | no |
| Current output signal | 4 mA ... 20 mA |
| | 20 mA ... 4 mA |
| Max. current output signal | 23 mA |
| Load | (U _L - 11 V) / 0,023 A |
| HART coding | FSK ± 0.5 mA |
| HART version | 7 |
| Transmission speed | 1200 Baud |
| Mains frequency filter | 50/60 Hz |
| Communication resistance | ≥ 250 Ω |
| Switch-on delay | ≈  s (HART) |
| | ≈  s (Measured value) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Test socket

| | |
|---------------|------|
| Max. diameter | 2 mm |
|---------------|------|

Ex data

| | |
|-----------------------|--------|
| Ex installation (EPL) | Gc |
| | Div. 2 |

Interfaces

Data communication (bypass)

| | |
|---------------------|------|
| Protocols supported | HART |
|---------------------|------|

Signaling

| | |
|----------------|-----------|
| Status display | LED (red) |
|----------------|-----------|

Dimensions

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

| | |
|---------------------|--|
| Dimensional drawing | |
| Width | 12.5 mm |
| Height | 112.5 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|-------|-----------------|
| Color | gray (RAL 7042) |
|-------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C -40 °C ... 70 °C (SIL active) |
| Ambient temperature (storage/transport) | -40 °C ... 100 °C |
| Altitude | ≤ 4000 m (Above sea level) |
| Climatic class | B2 |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

ATEX

| | |
|----------------|------------------------------|
| Identification | ⊕ II 3G Ex nA IIC T6...T4 Gc |
|----------------|------------------------------|

UL, USA/Canada

| | |
|----------------|---------------------|
| Identification | UL 61010 Recognized |
|----------------|---------------------|

FM

| | |
|----------------|--|
| Identification | NI, Class I, Div. 2, Groups A, B, C, D |
|----------------|--|

CSA

| | |
|----------------|---------------------------------------|
| Identification | NI / Class I / Div. 2 / ABCD T6/T5/T4 |
|----------------|---------------------------------------|

Shipbuilding approval

| | |
|-------------|-------------------|
| Certificate | DNV GL TAA00002GX |
|-------------|-------------------|

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|---|
| Identification | 2 |
|----------------|---|

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Systematic Capability

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

Shipbuilding data

| | |
|-------------|---|
| Temperature | D |
| Humidity | B |
| Vibration | A |
| EMC | B |
| Enclosure | A |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

MACX MCR-TS-I-OLP - Temperature measuring transducer




2908662

<https://www.phoenixcontact.com/us/products/2908662>

Drawings

Dimensional drawing




MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>



MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908662>



cUL Recognized
Approval ID: FILE E 198586



UL Recognized
Approval ID: FILE E 198586



EAC
Approval ID: RU*DE.*08.B.01608/19



DNV GL
Approval ID: TAA00002GX



Functional Safety
Approval ID: Z10 029429 0021



DNV
Approval ID: TAA00002GX



CSA
Approval ID: 70107976



FM approved
Approval ID: FM17US0110X

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210129 |
| ECLASS-15.0 | 27210129 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002919 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 41112100 |
|-------------|----------|

MACX MCR-TS-I-OLP - Temperature measuring transducer



2908662

<https://www.phoenixcontact.com/us/products/2908662>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 4382a4b0-b4e8-44e4-a92a-f8398f3d6173 |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com