

EMG 45-DIO 8E/LP - Diode block

2954798

<https://www.phoenixcontact.com/us/products/2954798>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Lamp test module, 2 diodes with common cathode: with 4 pairs, for individual wiring



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2954798 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | C440 |
| Product key | DK66M1 |
| GTIN | 4017918085131 |
| Weight per piece (including packing) | 82.7 g |
| Weight per piece (excluding packing) | 82.7 g |
| Customs tariff number | 85411000 |
| Country of origin | DE |

EMG 45-DIO 8E/LP - Diode block



2954798

<https://www.phoenixcontact.com/us/products/2954798>

Technical data

Product properties

| | |
|--------------|---------------------|
| Product type | Lamp testing module |
|--------------|---------------------|

Insulation characteristics

| | |
|------------------|---|
| Pollution degree | 2 |
|------------------|---|

Input data

Diode

| | |
|------------------------------------|---|
| Description of the input | 8 diodes, groups of 2 diodes with common cathode: Version: with 4 pairs, for individual loads |
| Diode type | 1 N 4007 |
| Max. operating voltage U_{max} | 250 V AC |
| Peak reverse voltage per diode | 1300 V |
| Reverse current per diode | $\leq 5 \mu\text{A}$ |
| Conducting state voltage per diode | approx. 0.8 V |
| Conducting state current per diode | 0.7 A (with single load) 0.4 A (with simultaneous loads) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

| | |
|--------|-------|
| Width | 45 mm |
| Height | 75 mm |
| Depth | 55 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

Approvals

CE

EMG 45-DIO 8E/LP - Diode block



2954798

<https://www.phoenixcontact.com/us/products/2954798>

| | |
|-------------|--------------|
| Certificate | CE-compliant |
| Note | and EN 61326 |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|-----------------------|--------------|

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

EMG 45-DIO 8E/LP - Diode block


2954798

<https://www.phoenixcontact.com/us/products/2954798>



Drawings

Circuit diagram



EMG 45-DIO 8E/LP - Diode block



2954798

<https://www.phoenixcontact.com/us/products/2954798>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2954798>



EAC

Approval ID: RU*DE*08.B.01841/19

EMG 45-DIO 8E/LP - Diode block



2954798

<https://www.phoenixcontact.com/us/products/2954798>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371010 |
| ECLASS-15.0 | 27371010 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000683 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151500 |
|-------------|----------|

EMG 45-DIO 8E/LP - Diode block



2954798

<https://www.phoenixcontact.com/us/products/2954798>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 83ae160f-893d-4ecc-9b8f-0ad1a8a19494 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com