

UM 45-D37SUB/S/FRONT/Q - Termination board

2959638

<https://www.phoenixcontact.com/us/products/2959638>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE SLIM LINE, with screw connection and D-subminiature pin strip, for assembly at a right angle on NS 35/7.5, 37 positions



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2959638 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C422 |
| Product key | DK21A2 |
| GTIN | 4017918086282 |
| Weight per piece (including packing) | 258.2 g |
| Weight per piece (excluding packing) | 257.5 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

UM 45-D37SUB/S/FRONT/Q - Termination board

2959638

<https://www.phoenixcontact.com/us/products/2959638>



Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Interface module |
| Number of positions | 37 |

Insulation characteristics: Air clearances and creepage distances

| | |
|---------------------|-----------------------|
| Insulation | Functional insulation |
| Oversupply category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|-------------------------|-----------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Current (per branch) | ≤ 2.5 A |
| Current (Total current) | ≤ 55.5 A |

Air clearances and creepage distances

| | |
|--------------------------|--------------------|
| Rated insulation voltage | 125 V |
| Rated surge voltage | 1.2 kV (1.2/50 µs) |

Connection data

Connection 1 (control level)

| | |
|----------------------------------|-----------------|
| Connection in acc. with standard | IEC 60807-2 |
| Connection method | D-SUB pin strip |
| Screw thread | UNC 4-40 |
| Number of connections | 1 |
| Number of positions | 37 |
| Insertion/withdrawal cycles | > 500 |
| Pitch | 2.77 mm |

Connection 2 (field level)

| | |
|---|--|
| Connection method | Screw connection |
| Stripping length | 9 mm |
| Screw thread | M3 |
| Number of positions | 38 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid (2 conductors with same cross section) | 0.2 mm ² ... 0.75 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| | 0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve) |
| | 0.25 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve) |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.2 mm ² ... 0.75 mm ² |
| | 0.25 mm ² ... 0.34 mm ² (Ferrule without plastic sleeve) |
| Conductor cross-section AWG | 24 ... 14 |

UM 45-D37SUB/S/FRONT/Q - Termination board

2959638

<https://www.phoenixcontact.com/us/products/2959638>



| | |
|-------------------|-------------------|
| Tightening torque | 0.4 Nm ... 0.5 Nm |
| Pitch | 5 mm |

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Dimensions

| | |
|-----------------|---------|
| Item dimensions | |
| Width | 45 mm |
| Height | 156 mm |
| Depth | 46.6 mm |

Material specifications

| | |
|-----------------------------|------------------|
| Color | green (RAL 6021) |
| Housing insulation material | PVC |

Environmental and real-life conditions

| | |
|--|------------------|
| Ambient conditions | |
| Degree of protection (Module) | IP20 |
| Degree of protection (Installation location) | ≥ IP54 |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Altitude | ≤ 2000 m |

Approvals

| | |
|-------------|----------------|
| UKCA | |
| Certificate | UKCA-compliant |

Standards and regulations

| | |
|---------------------------------------|----------------|
| Air clearances and creepage distances | |
| Standards/regulations | EN IEC 60664-1 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

UM 45-D37SUB/S/FRONT/Q - Termination board


2959638

<https://www.phoenixcontact.com/us/products/2959638>



Drawings

Circuit diagram



UM 45-D37SUB/S/FRONT/Q - Termination board

2959638

<https://www.phoenixcontact.com/us/products/2959638>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002780 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UM 45-D37SUB/S/FRONT/Q - Termination board

2959638

<https://www.phoenixcontact.com/us/products/2959638>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com