


IB IL SSI-IN-PAC - Function module



2819574
<https://www.phoenixcontact.com/us/products/2819574>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline measurement terminal block for absolute encoders, complete with accessories (connector and labeling field), 1 input for absolute rotation or position measurement systems, with SSI interface

Your advantages


- 1 single or multiturn encoder with up to 25 bit resolution can be connected
- Transmission frequency up to 1 MHz
- Shield connection
- 5 V encoder supply including monitoring
- Parity monitoring
- Rotation can be reversed
- Gray or binary code

Commercial data

Item number	2819574
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI161
GTIN	4017918941154
Weight per piece (including packing)	94.2 g
Weight per piece (excluding packing)	71 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Dimensions

Dimensional drawing		
Width		12.2 mm
Height		135 mm
Depth		71.5 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

System properties

Module

ID code (dec.)	95
ID code (hex)	5F
Length code (hex)	02
Length code (dec)	02
Process data channel	32 bit
Input address area	4 Byte
Output address area	4 Byte
Register length	4 Byte
Required parameter data	6 Byte
Required configuration data	5 Byte

Input data

Absolute encoder

Number of inputs	1
------------------	---

IB IL SSI-IN-PAC - Function module



2819574

<https://www.phoenixcontact.com/us/products/2819574>

Adjustable resolution	25 bit (maximum)
Transmission frequency	100 kHz
	200 kHz
	400 kHz
	800 kHz
	1 MHz

Digital

Connection technology	Spring-cage connection
-----------------------	------------------------

Output data

Digital

Number of outputs	1
-------------------	---

Product properties

Product type	I/O component
Product family	Inline
Type	modular

Electrical properties

Maximum power dissipation for nominal condition	0.55 W
---	--------

Supply

Drawing encoder supply voltage	Main circuit U_M
Encoder supply voltage	5 V DC
Encoder supply current	max. 250 mA
I/O voltage	24 V AC
Max. current consumption	35 mA (typical)

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 28 mA

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 66 mA

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross-section rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.08 mm ² ... 1.5 mm ²

IB IL SSI-IN-PAC - Function module



2819574

<https://www.phoenixcontact.com/us/products/2819574>

Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	75 % ... 85 %
Permissible humidity (storage/transport)	75 % ... 85 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL SSI-IN-PAC - Function module




2819574


<https://www.phoenixcontact.com/us/products/2819574>

Drawings

Dimensional drawing



Connection diagram



IB IL SSI-IN-PAC - Function module



2819574

<https://www.phoenixcontact.com/us/products/2819574>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2819574>



cULus Listed

Approval ID: E199827

IB IL SSI-IN-PAC - Function module



2819574

<https://www.phoenixcontact.com/us/products/2819574>

Classifications

ECLASS

ECLASS-13.0	27242605
ECLASS-15.0	27242605

ETIM

ETIM 9.0	EC001601
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d4eb2f1f-7643-4f03-afdd-48dc05d420b4