

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ethernet Smart Managed Compact Switch with eight 10/100 Mbps RJ45 ports



## Product description

The Smart Managed Compact Switch (SMCS) is an Ethernet switch suitable for industrial applications with eight Fast Ethernet ports in RJ45 format.

## Your advantages

- RSTP
- MRP (client and manager)
- SNMP
- VLANs
- Web-based management, SNMP

## Commercial data

Item number	2989226
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN17
Product key	DNN122
GTIN	4046356451864
Weight per piece (including packing)	853.3 g
Weight per piece (excluding packing)	650 g
Customs tariff number	85176200
Country of origin	DE

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



## Technical data

### Dimensions

Width	128 mm
Height	110 mm
Depth	69 mm

### Material specifications

Color	gray aluminum
-------	---------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

Ethernet (RJ45)	
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	8 (RJ45 ports)

### Serial (RS-232)

Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)
-------------------	---

### Product properties

Product type	Switch
Product family	Managed Switch SMCS
Type	Block design
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).

### Insulation characteristics

Protection class	III (VDE 0106)
------------------	----------------

### Switch functions

Diagnostic functions	RMON History N:1-Portmirroring LLDP (Link Layer Discovery Protocol) SNMP-Traps ACD (Address Conflict Detection)
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



	classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).
Signal contact control voltage	24 V (typical)
Signal contact control current	600 mA (maximum)
PROFINET conformance class	Conformance Class B
PROFINET device function	PROFINET device
Filter functions	<p>Fast Startup</p> <p>Quality of Service (4 priority classes)</p> <p>Port-Priorisierung</p> <p>VLAN</p> <p>IGMP Snooping (128 groups)</p> <p>IGMP Query</p> <p>Auto-Query-Port</p> <p>Extended Multicast Filtering</p> <p>Static Multicast Filtering</p>
MAC address table	4000
Management	<p>Web-based management (HTTP)</p> <p>SNMP v1/v2</p> <p>Serial interface (V.24)</p>
Redundancy	<p>MRP (Media Redundancy Protocol)</p> <p>RSTP (Rapid Spanning Tree Protocol)</p> <p>FRD (Fast Ring Detection)</p> <p>Large Tree Support</p>
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
Supported browsers	Internet Explorer 5.5 or higher
Additional functions	<p>BootP</p> <p>DHCP-Client</p>
Time synchronization	SNTP
Security functions	
Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).

## Electrical properties

Current consumption	600 mA
Local diagnostics	<p>US1/2 Supply voltage US1, US2 Green LED</p> <p>FAIL Div. LED red</p> <p>LINK Link status Green LED</p> <p>ACT/MODE Receiving/sending telegrams Green LED</p> <p>SPD/MODE Data transmission speed Green/orange LED</p> <p>FD/MODE Duplex mode Green LED</p>

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



Maximum power dissipation for nominal condition	14.4 W
Test section	500 V DC 1 min
Transmission medium	Copper

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	18 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Typical current consumption	240 mA (at U <sub>S</sub> = 24 V DC)
Current consumption	600 mA

## Function

Signal contact control voltage	24 V (typical)
Signal contact control current	600 mA (maximum)

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (2000 m above mean sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

## Standards and regulations

Free from substances that could impair the application of coating	Yes
---	-----

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion A
	IEC 61000-4-3 (electromagnetic fields) Criterion A
	IEC 61000-4-4 (burst) Criterion A
	IEC 61000-4-5 (surge) Criterion A
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
Noise immunity	EN 61000-6-2:2005

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



## Noise emission

Standards/regulations

EN 61000-6-3+A11

## System properties

### Functionality

Basic functions

Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).

### System requirements

Supported browsers

Internet Explorer 5.5 or higher

### Signaling

Status display

LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



## Classifications

### UNSPSC

UNSPSC 21.0

43222612

# FL SWITCH SMCS 8TX - Industrial Ethernet Switch

2989226

<https://www.phoenixcontact.com/us/products/2989226>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)