

IBS OPTOSUB-F/R-LK-OPC - Fiber optic adapter

2863999

<https://www.phoenixcontact.com/us/products/2863999>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS fiber optic adapter, for converting the remote IN interface to fiber optics, FO output right, correction of the optical transmission power

Commercial data

Item number	2863999
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DREDDA
GTIN	4046356046381
Weight per piece (including packing)	58.8 g
Weight per piece (excluding packing)	49.74 g
Country of origin	DE

IBS OPTOSUB-F/R-LK-OPC - Fiber optic adapter

2863999

<https://www.phoenixcontact.com/us/products/2863999>



Technical data

Product properties

Product type	Media converter
--------------	-----------------

Interfaces

Signal	INTERBUS
--------	----------

Data: optical FO

Connection method	F-SMA
Wavelength	660 nm
Transmission medium	FO

Data: Incoming remote bus

Bus system	INTERBUS
Transmission speed	500 kbps
Connection method	D-SUB 9 plug
Transmission length	35 m (50 m system without optical path diagnostics) 50 m (70 m system with optical path diagnostics)

Dimensions

Width	65 mm
Height	16 mm
Depth	59 mm

Material specifications

Color	green
-------	-------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20

IBS OPTOSUB-F/R-LK-OPC - Fiber optic adapter

2863999

<https://www.phoenixcontact.com/us/products/2863999>



Classifications

ETIM

ETIM 8.0

EC001423

UNSPSC

UNSPSC 21.0

32151700

IBS OPTOSUB-F/R-LK-OPC - Fiber optic adapter

2863999

<https://www.phoenixcontact.com/us/products/2863999>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com